



designed to be better.

15 Amp NEMA L615 Plug - Black Back, White Front Body

PSL615P

15amp 250volt Extra-hard Use (ehu) Turnlok Yellow

Where to buy

0






Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Top 5 Resources

-  Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2 (Cutsheet)
-  Commercial & Industrial Products (Brochure)
-  Plugs & Connectors (Brochure)

specifications

General Info

- Color: Black, White
- Type: Plug
- Special Features: Extra-hard Use

Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Diameter U S: 1.516"
- Length: 2.617"

Technical Information

- Amps: 15 Amp
- NEMA Configuration Number: L615
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)
-  Plugs & ConnectorsPDF (1.93mb)

CUTSHEET

-  Turnlok EHU Plugs & Connectors 3 Wire, SF1702R2PDF (309.83kb)