

## FEATURES & SPECIFICATIONS

**INTENDED USE** — Ideal for damp/wet locations such as outdoor venues, canopies and locker rooms. **Certain airborne contaminants can diminish integrity of polycarbonate.** [Click here for Acrylic and Polycarbonate Environmental Compatibility table for suitable uses.](#)

**CONSTRUCTION** — Light gray, fully gasketed polycarbonate housing with stainless steel captive latches to provide a waterproof seal. 3/8" wet location fitting provided on one end.

**OPTICS** — UV-stabilized, high-impact, clear polycarbonate lens for maximum light output and high-impact resistance.

**ELECTRICAL** — High-efficiency LEDs with 80% lumen maintenance at 60,000 hours; predicted life of more than 50,000 hours.

**INSTALLATION** — Mounting hardware for surface mounting to ceiling or wall (horizontally or vertically) included. Not designed for continuous row mounting or daisy chaining.

**LISTINGS** — UL Listed. For use in wet locations under covered ceilings. For use in ambient temperatures from -22°F (-30°C) to 77°F (25°C). IP65 rated.

**WARRANTY** — 5-year limited warranty. Complete warranty terms located at [www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Actual performance may differ as a result of end-user environment and application.

Actual wattage may differ by +/- 10% when operating between 120-277V +/- 10%.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select

# LED Wet Location Striplight



Specifications					
All dimensions are shown in inches (centimeters) unless otherwise noted.					
LUMENS	LENGTH	WIDTH	DEPTH	WEIGHT	COMPARABLE LIGHT SOURCE
1800	47-1/2 (120.7)	2 3/8 (6.0)	3 (7.6)	4.4 lbs (2.0 kg)	1 - 32W T8

### ORDERING INFORMATION

Catalog number	UPC	Description	Lumens	Wattage	Voltage	Color temperature	Pallet quantity	Standard carton quantity
XWMLLED	753573956365	LED wet location striplight	1800	24	120 - 277	4000K, 88 CRI	60	1

