



designed to be better.

[Search](#)

# Power Outlet Receptacle Openings, One Gang, 302 Stainless Steel

SS720

One Gang Power Outlet Receptacle Opening, 1.5938" hole for 1.5625" diameter device - 2 mtg. holes, Smooth Metal.

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

## features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## Top 5 Resources

 Stainless Steel Wall Plates, SF2502R1 (Cutsheet)

## specifications

### General Info

- Size: Standard
- Type: Single

### Listing Agencies/Third Party Information

- cU Rus: No
- U N SPS C: 39121704

### Dimensions

- Diameter U S: 1.5938" Hole

### Technical Information

- Material: Stainless Steel
- Capacity: 1-gang

### Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
- 



## resources

### CUTSHEET

 Stainless Steel Wall Plates, SF2502R1PDF (367.16kb)