

Technical Specifications Heavy-Duty Tamper-Resistant Decorator Receptacles


2 Pole, 3 Wire Grounding 15 & 20A, 125V




Typical Specifications

Manufacturer's Identification: Legrand/Pass & Seymour TR26362
 Description: PlugTail™ Straight Blade Duplex Receptacle – Heavy-Duty Tamper-Resistant Decorator
 Type: 2 Pole, 3 Wire Grounding
 Rating: 15A, 125V
 Configuration: NEMA 5-15R
 3rd Party Compliance: UL Listed, File Number E140596, Standard UL498, Federal Specification WC596, CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42. Conforms to NEMA WD-1 and WD-6.

Catalog Number	Color	Rating	NEMA Config. No.	Catalog Number	Color	Rating	NEMA Config. No.
<input type="checkbox"/> TR26262I	Ivory	15A 125V	5-15R	<input type="checkbox"/> TR26262HGI	Ivory	15A 125V	5-15R
<input type="checkbox"/> TR26262W	White	15A 125V	5-15R	<input type="checkbox"/> TR26262HGW	White	15A 125V	5-15R
<input type="checkbox"/> TR26262	Brown	15A 125V	5-15R	<input type="checkbox"/> TR26262HGGRY	Gray	15A 125V	5-15R
<input type="checkbox"/> TR26262GRY	Gray	15A 125V	5-15R	<input type="checkbox"/> TR26262HGRED	Red	15A 125V	5-15R
<input type="checkbox"/> TR26262BK	Black	15A 125V	5-15R	<input type="checkbox"/> TR26262HGLA	Lt. Al.	15A 125V	5-15R
<input type="checkbox"/> TR26262RED	Red	15A 125V	5-15R	<input type="checkbox"/> TR26362HGI	Ivory	20A 125V	5-20R
<input type="checkbox"/> TR26262LA	Lt. Al.	15A 125V	5-15R	<input type="checkbox"/> TR26362HGW	White	20A 125V	5-20R
<input type="checkbox"/> TR26362I	Ivory	20A 125V	5-20R	<input type="checkbox"/> TR26362HGGRY	Gray	20A 125V	5-20R
<input type="checkbox"/> TR26362W	White	20A 125V	5-20R	<input type="checkbox"/> TR26362HGBK	Black	20A 125V	5-20R
<input type="checkbox"/> TR26362	Brown	20A 125V	5-20R	<input type="checkbox"/> TR26362HGRED	Red	20A 125V	5-20R
<input type="checkbox"/> TR26362GRY	Gray	20A 125V	5-20R	<input type="checkbox"/> TR26362HGLA	Lt. Al.	20A 125V	5-20R
<input type="checkbox"/> TR26362BK	Black	20A 125V	5-20R				
<input type="checkbox"/> TR26362RED	Red	20A 125V	5-20R				
<input type="checkbox"/> TR26362LA	Lt. Al.	20A 125V	5-20R				



TR26362I



TR26362HGI

Performance

Electrical

Dielectric Voltage Withstands 2000V minimum
 Maximum Working Voltage 250V
 Current Interrupting Certified for current interrupting at full-rated current
 Temperature Rise Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical

Terminal Identification Terminal identification in accordance with UL498 (Brass, White, Green)
 Terminal Accommodation #14 – #10 AWG copper conductor only
 Product Identification Ratings are a permanent part of the device

Environmental

Flammability UL94 V2
 Operating Temperature Maximum continuous +60°C, minimum -40°C without impact

Materials

Face	Nylon	Tamper Shutter	Thermoplastic
Back Body	Nylon	Terminal Screws	#10 Tri-Drive Brass (Neutral = Nickel-Plated Steel)
Line Contacts	.036 688 Brass	Ground Screw	#10 Hex Tri-Drive Brass
Mounting Strap	Plated Steel	Auto-Ground Clip	Steel
Ground Contacts	Strap with Integral Ground	Mounting Screws	Tri-Drive Steel
Pressure Plate	.031 260 Brass		

Consult Straight Blade Section B for complete compliance listing.

Project
Location/Type



NEMA 5-15R



NEMA 5-20R