

REPORT CARD

(For fixtures using the Lutron
Hi-lume® A-Series LED driver)



***REQUIRED FIELDS**

Manufacturer:*	
Website:*	
Applicable model numbers:*	
Date:*	

Fixture manufacturer's description		<input type="checkbox"/> Cove/Strip light <input type="checkbox"/> Pucklight <input type="checkbox"/> Downlight <input type="checkbox"/> Sconce <input type="checkbox"/> Linear LEDs <input type="checkbox"/> Troffer fixture <input type="checkbox"/> Light engine <input type="checkbox"/> Wallwash <input type="checkbox"/> Pendant
Type of fixture:*	Choose from list at right ►	
Operating voltage:	120V – 277V	
Control type:	EcoSystem® / 3-wire	
Dimming range:	100% – 1%	
Input power (max.):*		

Driver manufacturer: Lutron Electronics
Product: Hi-lume A-Series LED driver



Compatible Lutron products

Product family	Part number		Fixtures per control		Measured light output range
	120V	277V	120V	277V	
NovaT [☆] ®	NTF-10-	NTF-10-277-	1 – 41	1 – 44	100% – 1%
	NTF-103P-	NTF-103P-277-	1 – 20	1 – 33	100% – 1%
Nova®	NF-10-	NF-10-277-	1 – 41	1 – 44	100% – 1%
	NF-103P-	NF-103P-277-	1 – 20	1 – 33	100% – 1%
Vareo®	VF-10-		1 – 20	—	100% – 1%
Skylark®	SF-10P-	SF-12P-277-	1 – 20	1 – 33	100% – 1%
	SF-103P-	SF-12P-277-3	1 – 20	1 – 33	100% – 1%
Diva®	DVF-103P-	DVF-103P-277-	1 – 20	1 – 33	100% – 1%
	DVSCF-103P-	DVSCF-103P-277-	1 – 20	1 – 33	100% – 1%
Ariadni®	AYF-103P-	AYF-103P-277-	1 – 20	1 – 44	100% – 1%
Vierti®	VTF-6A-		1 – 15	1 – 33	100% – 1%
Maestro®	MAF-6AM-	MAF-6AM-277-	1 – 15	1 – 33	100% – 1%
	MSCF-6AM-	MSCF-6AM-277-	1 – 15	1 – 33	100% – 1%
Maestro Wireless®	MRF2-F6AN-DV-		1 – 15	1 – 33	100% – 1%
RadioTouch®	RTA-RX-F-		1 – 41	1 – 88	100% – 1%
Spacer System®	SPSF-6A-	SPSF-6A-277-	1 – 15	1 – 33	100% – 1%
	SPSF-6AM-	SPSF-6AM-277-	1 – 15	1 – 33	100% – 1%
Lyneo® Lx	LXF-103PL-	LXF-103PL-277-	1 – 20	1 – 33	100% – 1%
RadioRA® 2	RRD-F6AN-DV-		1 – 15	1 – 33	100% – 1%
HomeWorks® QS	HQRD-F6AN-DV		1 – 15	1 – 33	100% – 1%
Interfaces*	PHPM-3F	PHPM-3F-DV	1 – 41	1 – 88	100% – 1%
	GRX-FDBI-16A		1 – 41	1 – 88	100% – 1%
PowPak™ dimming module with EcoSystem	RMJ-ECO32-DV-B		32 per EcoSystem link		100% – 1%
Energi Savr Node™ with EcoSystem	QSN-1ECO-S, QSN-2ECO-S		63 per EcoSystem link		100% – 1%
GRAFIK Eye® QS with EcoSystem	QSG-_P120		64 per EcoSystem link		100% – 1%
Quantum®	Various		64 per EcoSystem link		100% – 1%

* For use with 3-wire controls or Commercial Systems, RadioRA Systems, or Home Systems applications.

NOTE: Low-end trim may need to be adjusted to achieve 1% dimming.

For information on low-end trim adjustment, consult installation instructions.