



Pass & Seymour

Straight Blade Receptacles Hard Use Tamper-Resistant 15 & 20A, 125V

TR5262, TR5362

Tamper-resistance in a construction grade receptacle – now with Federal Specification listing!

Tamper-resistant child safety receptacles that conform to 2008 NEC Article 406.11 are now available in construction grade. They offer a UL Federal Specification WC596 listing at an exceptional value. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces, and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Screw-pressure-plate back wiring ensures excellent electrical connections and easy installation.




Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.



Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability. Two back wire holes for more wiring flexibility.

TR5362-LA

Field Uses/Vertical Markets

- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

SF314R1 — Updated June 2008 — For latest specs visit www.legrand.us/passandseymour

Straight Blade Receptacles Hard Use Tamper-Resistant 15 & 20A, 125V

Ordering Information

Catalog Number	Rating A.	V.	Color	NEMA Config. No.
Duplex Receptacles Back & Side Wire				
TR5262-I	15	125	Ivory	5-15R
TR5262-W	15	125	White	5-15R
TR5262	15	125	Brown	5-15R
TR5262-GRY	15	125	Gray	5-15R
TR5262-BK	15	125	Black	5-15R
TR5262-RED	15	125	Red	5-15R
TR5262-LA	15	125	Light Almond	5-15R
TR5362-I	20	125	Ivory	5-20R
TR5362-W	20	125	White	5-20R
TR5362	20	125	Brown	5-20R
TR5362-GRY	20	125	Gray	5-20R
TR5362-BK	20	125	Black	5-20R
TR5362-RED	20	125	Red	5-20R
TR5362-LA	20	125	Light Almond	5-20R



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.


Straight Blade Receptacles Hard Use Tamper-Resistant 15 & 20A, 125V



Technical Specifications

3rd Party Compliance
UL Listed, File Number E140596, Standard UL498, Federal Specification WC596, CSA/CUL Approved, Standard CSA-C22.2 No. 42.

Performance	
Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Maximum Continuous Current	TR5262 = 15A TR5362 = 20A
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Accommodation	#14 - #10 AWG copper conductor only
Product Identification	Amperage, Voltage, 3rd Party Compliance
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact




**Dimensions for
15 & 20 Amp**

Materials			
Face	Nylon	Terminal Screws	#8 Tri-Drive Brass (Neutral = Nickel-Plated Steel)
Back Body	PVC	Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Line Contacts	.032 Olin 688 Brass	Assembly Drive Screw	Zinc-Plated Steel
Mounting Strap	.042 Zinc-Plated Steel	Auto-Ground Clip	Stainless Steel
Ground Contacts	.040 Olin 688 Brass	Mounting Screws	Tri-Drive Steel
Pressure Plate	.080 Steel		
Tamper-Resistant Shutters	Thermoplastic		

Warranty


1 Year

Complementary Devices & Accessories




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant
- Extra Heavy-Duty Tamper-Resistant Hospital Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Extra Heavy-Duty
- Extra Heavy-Duty Lighted
- Extra Heavy-Duty Security
- Extra Heavy-Duty Locking
- Hard Use
- Commercial Grade



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

Also available...

- Light Almond Devices
- Hospital Grade Devices
- TVSS & Isolated Ground Devices
- Lighting & Fan Controls
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295,3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF314R1 — Updated June 2008 — For latest specs visit www.legrand.us/passandseymour