

GROUP M



600 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
3.0	T2A795161S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	NA	55-F
6.0	T2A795171S	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	NA	55-F
9.0	T2A795181S	14.03 (38.8)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	55-F
15.0	T3795191S	18.86 (47.9)	20.30 (51.6)	9.03 (22.9)	250 (113.0)	F ①	NA	NA	55-I
30.0	TP795203S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	400 (181.0)	F ①	NA	WSA2	51-E
45.0	TP795213S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	425 (193.0)	F ①	NA	WSA2	51-E
75.0	TP795223S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	700 (318.0)	F ①	NA	WSA2	51-E
112.5	TP795233S	35.47 (90.1)	31.90 (81.0)	26.88 (68.3)	750 (340.0)	F	NA	WSA3	51-E
150.0	TP795243S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	1125 (510.0)	F	NA	WSA4	51-E

Notes: 3.0 through 15.0 kVA units are encapsulated (TP1 exempt), 30.0 through 150.0 kVA are TP1 compliant

GROUP O

208 DELTA PRIMARY VOLTS — 208Y/120 SECONDARY VOLTS — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
3.0	T2A792681S	10.38 (26.4)	12.37 (31.4)	7.47 (19.0)	75 (34.0)	W	0.75-1.25 (1.9-3.2)	NA	60-F
6.0	T2A792691S	11.83 (30.0)	14.17 (36.0)	8.82 (22.4)	140 (63.5)	W	0.75-1.25 (1.9-3.2)	NA	60-F
9.0	T2A792701S	14.03 (36.0)	17.77 (45.1)	11.52 (29.3)	180 (81.6)	W	0.75-1.25 (1.9-3.2)	NA	60-F
15.0	T3-792711S	18.86 (48.0)	20.30 (51.6)	9.03 (22.9)	245 (111.0)	F ①	NA	NA	60-I
30.0	TP792724S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	300 (136.0)	F ①	NA	WSA1	61-E
45.0	TP792734S	25.48 (64.7)	24.39 (61.9)	19.37 (49.2)	365 (166.0)	F ①	NA	WSA1	61-E
75.0	TP792744S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	500 (227.0)	F ①	NA	WSA2	61-E

Notes: 3.0 through 15.0 kVA units are encapsulated (TP1 exempt), 30.0 through 75.0 kVA units are TP1 compliant

GROUP P

600 DELTA PRIMARY VOLTS — 240 DELTA/120 TAP SECONDARY VOLTS — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
30.0	TP131423S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	299 (135.6)	F ①	NA	WSA1	69-E
45.0	TP131433S	25.48 (64.7)	24.39 (61.9)	19.37 (49.2)	353 (160.1)	F ①	NA	WSA1	69-E
75.0	TP131443S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	463 (210.0)	F ①	NA	WSA2	69-E

Notes: 30.0 through 75.0 kVA units TP1 compliant

GROUP Q

240 DELTA PRIMARY VOLTS — 480Y/277 SECONDARY VOLTS — 3Ø, 60 Hz

kVA	CATALOG NO.	APPROX. DIMENSIONS Inches (Cm.)			APPROX. SHIP WEIGHT Lbs. (Kg.)	TYPE MTG. W – Wall F – Floor	KNOCKOUTS Inches (Cm.)	WEATHER SHIELD P/N	Wiring Diagrams & Design Figures Begin on Page 154
		HEIGHT	WIDTH	DEPTH					
15.0	T3-796931S	18.86 (48.0)	20.30 (51.6)	9.03 (22.9)	245 (111.1)	F ①	NA	NA	70-I
30.0	TP796944S	25.50 (64.8)	24.39 (61.9)	19.37 (49.2)	330 (149.7)	F ①	NA	WSA1	71-E
45.0	TP796954S	25.48 (64.7)	24.39 (61.9)	19.37 (49.2)	380 (172.4)	F ①	NA	WSA1	71-E
75.0	TP796964S	29.41 (74.7)	28.15 (71.5)	22.37 (56.8)	455 (206.4)	F ①	NA	WSA2	71-E
112.5	TP796974S	35.47 (90.1)	31.90 (81.0)	26.88 (68.3)	687 (311.6)	F	NA	WSA3	71-E
150.0	TP796984S	41.52 (105.5)	32.90 (83.6)	29.87 (75.9)	973 (441.3)	F	NA	WSA4	71-E

Notes: 15 kVA unit encapsulated (TP1 exempt), 30.0 through 150.0 kVA TP1 compliant

① Wall mounting brackets are available for these sizes, refer to page 165.