



A Marley Engineered Products Brand

470 Beauty Spot Rd. E, Bennettsville, SC 29512

SUBMITTAL SHEET SRA ARCHITECTURAL SERIES SMALL ROOM HEATERS

SRA ARCHITECTURAL SERIES - SMALL ROOM HEATERS


SELECTION CHART

CATALOG NUMBER	VOLTS*	WATTS**	BTU/HR.	AMPS
SRA1012DSAG	120	1000	3413	8.3
		500	1706	4.2
SRA1512DSAG	120	1500	5119	12.5
		750	2560	6.3
SRA1812DSAG	120	1800	6143	15
SRA1527DSAG	277/240	1500/1125	5119/3839	5.4/4.7
		750/563	2560/1918	2.7/2.3
SRA2020DSAG	208	2000	6826	9.6
		1000	3413	4.8
SRA2024DSAG	240/208	2000/1500	6826/5119	8.4/7.2
		1000/750	3413/2560	4.2/3.6
SRA2027DSAG	277/240	2000/1500	6826/5119	7.2/6.3
		1000/750	3413/2560	3.6/3.1

*Single phase, 60 Hz

** Factory Wired for Full Wattage, Field Convertible to Half Wattage.

CAPACITIES
500, 562, 750, 1000, 1125, 1500 or 2000 Watts 120, 208, 240 or 277V 1Ø Only



Thermostat Range: 40 - 90 °F
Air Movement: 65 CFM



FILE #E21609

SRASMAG	Surface mounting sleeve. Fits around back box of SRA heaters for surface mounted installations.
SRAS1AG SRAS2AG	1" or 2" semi-recessed sleeve to fit around exposed back box in semi-recessed installations.

MOUNTING LIMITATIONS:

1. For wall mounting - Do not install back box closer than 2 inches from floor or adjacent wall.
2. For ceiling - Do not install back box closer than 12 inches from adjacent wall.
3. Do not install heater behind towel rack, behind door, in floor, in closet or where air flow may be obstructed.

ITEM	QTY.	CATALOG NUMBER	TAG	WATTS	VOLTS	Ø	AMPS	BUILT-IN CONTROLS

ACCESSORIES AND CONTROLS

ITEM	QTY.	CAT. NO.	TAG	DESCRIPTION

SUBMITTED BY:	DATE


APPROVED BY:	DATE



A Marley Engineered Products Brand

470 Beauty Spot Rd. E, Bennettsville, SC 29512

DIMENSIONS



ARCHITECT'S & ENGINEER'S SPECIFICATIONS *

The heating equipment shall include an electric automatic SRA Series fan-forced air heater suitable for small area heating as manufactured by Berko, A Marley Engineered Products Brand, Bennettsville, SC. Heaters shall be UL Listed.

The heater shall be designed for surface or recessed wall mounting in any position and for ceiling mounting. For surface mounting a Berko SRASMAG surface mounting sleeve shall be used. For semi-recessed installation a Berko SRAS1AG or SRAS2AG semi-recessed sleeve shall be used.

BACK BOX: The back box shall be designed for duty as a recessed rough-in box in either masonry or frame construction and also when mounting directly to the surface of the finished walls in surface mounting installations. The back box shall be commercial grade galvanized steel and shall contain knock outs through which field wiring leads are brought and connected to pigtails of the pre-installed female disconnect receptacle. Connecting of the male plug of the inner frame completes the wiring of the heater.

INNER FRAME ASSEMBLY: The inner frame assembly shall consist of a commercial grade steel chassis on which are mounted the heating element, fan motor and blade, thermostat, fan delay and thermal cut out. The inner frame assembly shall be completely pre-wired with the leads terminating in a male plug, thus facilitating positive disconnect and easy removal for service without disturbing the back box or field wiring.

HEATING ELEMENT: The heating element shall be guaranteed for five years and shall be of nonglowing design consisting of a special resistance wire enclosed in a steel sheath to which steel plate fins are brazed. The element shall cover the entire air discharge area to ensure uniform heating of all discharge air.

MOTOR AND CONTROLS: The fan motor shall be impedance protected, permanently lubricated and with totally enclosed rotor.

Fan delay shall be bi-metallic, snap-action type and shall activate fan after heating element reaches operating temperature, and continue to operate the fan after the thermostat is satisfied and until all heated air has been discharged. The thermostat shall be single pole on all models. Thermal cutout shall be bi-metallic, snap-action type designed to shut off heater in the event of over heating.

DISCONNECT SWITCH: A built-in double pole single throw disconnect switch shall be provided for positive disconnect of power supply. It is completely concealed behind the front cover.

FRONT COVER: The louvered front cover shall be of commercial grade steel finished in Statuary Bronze.

TAMPER-PROOF INSTALLATION: Optional front cover without the hole for the thermostat knob provide full tamper-proof installation.

SURFACE MOUNTING SLEEVE: The surface mounting sleeve shall be of commercial grade steel, designed to mount around the back box for a finished surface installation. Slot knock outs shall be provided for power supply conduit. Semi-recessed sleeves shall be available for semi-recessed installation in walls less than 3-1/2 inches thick.

FINISH: All sheet metal parts, except the galvanized steel back box shall be phosphatized, then completely painted by a polyester powder coat finish.

* Berko reserves the right to change specifications without prior notice.