


Technical Specifications Weather-Resistant Commercial Grade Receptacles

15 & 20A, 125 & 250V

Pass & Seymour



Typical Specifications	
Manufacturer's Identification: Pass & Seymour/Legrand WR20TR	
Description: Straight Blade Duplex Receptacle – Weather-Resistant Commercial Grade	
Type: 2 Pole, 3 Wire Grounding	
Rating: 20A, 125V	
Configuration: NEMA 5-20R	
3rd Party Compliance: cUL Listed, File Number E140596, Standard UL498, Standard CSA-C22.2 No. 42. Conforms to NEMA WD-1 and WD-6.	



WR20TRW

Catalog Number	Color	Rating	NEMA Config. No.	Catalog Number	Color	Rating	NEMA Config. No.
<input type="checkbox"/> WR20TRI	Ivory	20A 125V	5-20R	<input type="checkbox"/> WR20TRGRY	Gray	20A 125V	5-20R
<input type="checkbox"/> WR20TRW	White	20A 125V	5-20R	<input type="checkbox"/> WR20TRLA	Lt. Al.	20A 125V	5-20R
<input type="checkbox"/> WR20TR	Brown	20A 125V	5-20R				

WR20TR models are Tamper-Resistant.

Performance			
Electrical			
Dielectric Voltage	Withstands 1500V minimum		
Maximum Working Voltage	125V		
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current		
Mechanical			
Terminal Identification	Terminal identification in accordance with UL498 (Brass, White, Green)		
Terminal Accommodation	#14 – #10 AWG copper conductor only		
Product Identification	Ratings are a permanent part of the device		
Environmental			
Flammability	UL94 V2		
Operating Temperature	Maximum continuous +50°C, minimum -40°C without impact		
Materials			
Face	UV Resistant Nylon	Ground Screw	#8 Hex Tri-Drive Nickel-Plated Steel
Back Body	PVC	Assembly Drive Screw	Zinc-Plated Steel
Line Contacts	.032 260 Brass	Auto-Ground Clip	Stainless Steel
Mounting Strap	.042 Nickel-Plated Steel	Mounting Screws	Tri-Drive Steel
Ground Contact	.040 260 Brass		
Terminal Screws	#8 Tri-Drive Brass (Neutral = Nickel-Plated Brass)		



NEMA 5-20R

Project
Location/Type