



Representative

**Catalog Number:** ASP20  
**Product ID:** 7TAH007890R1135  
**UPC Number:** 78378661066  
**Status:** Active

Type ASP Aluminum Splice, Wire Size Max 35kV, Wire Size 2/0 Str, Length 2-1/2 Inch, Tin Plated, Die Color Code Olive

- Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification. Prefilled with oxide inhibiting compound.

### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Aluminum Splice
Special Features	Made of high-conductivity seamless aluminum tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Material	Aluminum
Finish	Tin Plated
Color	Olive
Voltage Rating	35KV

### European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Useful for stranded conductors	Y
Material	Other
Surface protection	Tinned
Insulation	None
Voltage row	Up to 35kV

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	50
Outer Dimensions (inches)	12.4x6.4x4.1
Weight Uom	7.19 lbs. per 100

### Documents / Support Tools

SDS US 1	sds-00012-tb2
Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)