

3800-OEM

Type 4: UL Recognized Components



UPC Code: 07847786882

Country of Origin: Mexico - *Eligible for ARRA funded projects > \$7,443,000



Brand Features

Leviton's Surge Protection Devices can be used individually or as part of a coordinated application strategy, to protect sensitive electronic equipment, in industrial, commercial and residential locations, from the stress and degradation inflicted by voltage transients. Leviton Surge Protection Devices are compliant with UL 1449 Standards. Leviton's outstanding Surge Protection Devices divert damaging voltage transients, or surges, away from electronic equipment. Transients are diverted away from sensitive micro circuitry, providing protection against catastrophic failure, costly downtime and data disruptions.

Item Description

120 Volt AC, 2 Pole, 3 Wire, Equipment Cabinet SPD Surge Protective Device, Wired-In Module, Surface Mounted, 6 Inch Pigtail Wired, in a NEMA 1 Enclosure

Technical Information

Electrical Specifications

Voltage: 125 VAC
Frequency: 50/60Hz
Surge Technology: MOV

Environmental Specifications

Operating Temperature: -10C to 60C
Storage Temperature: -20°C to 85°C
Flammability: Rated V-0 per UL94
Relative Humidity: 5% to 95% non-condensing

Material Specifications

Enclosure Material: Polycarbonate

Mechanical Specifications

Connection Type: 6" Pigtails
Diagnostics: Indicator Light & Audible Alarm

Performance Data

MCOV: 130V
Joules Rating: 600
Nominal Discharge Current Rating: 3kA
Maximum Surge Current, Per Mode (Per Phase): 36kA (L-N:24kA, L-G:12kA)
VPR: L-N:700V, L-G:700V, N-G:600V
Noise Filtering: -10dB to -15dB (@100K-100MHz)
Protection Mode: 3 Mode

Product Features

Voltage: 120 Volt AC
Diagnostics: LED
Mounting Type: Surface
Wiring: 6 Inch Pigtail
Joules Rating: 280
MCOV: 135V AC
UL1449 Impulse Perm Wired Test L-N/L-G/N-G: 500/500/500
Max 1-Pulse Transient Current L-N/L-G/N-G: 1.3kA/6.5kA/6.5kA
Noise Rejection: -35 dB at 5kHz-5MHz
Circuitry: MOV-Based Suppression
Standards and Certifications: UL1449 / CSA / ANSI/IEEE Cat ABC

Standards and Certifications

Agency Certifications: UL & CSA Recognized Components
ANSI/IEEE Category A & B: C-62.41 & C-62.45
NOM: ETL Certified to NOM-001

Warranty

Product Warranty: 10-Year Limited

SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: 1-800-323-8920 · FAX: 1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): 1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: 1-800-469-7890 ·

FAX: 1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012-2016 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.



Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to: www.leviton.com/international/contacts/

**Buy American Compliant Logo -- The American Recovery And Reinvestment Act of 2009 ("ARRA") provides federal grants and loans for projects throughout the country. Section 1605 of the Act, named the "Buy American" provision, requires that certain materials and manufactured products used in projects funded by the Act be manufactured in the United States. The appearance of the Recovery Act Logo in relation to a Leviton product is only intended to reflect that such product may be used in an ARRA funded project. It does not mean that such product or Leviton is sponsored or endorsed by, or that Leviton receives funds from, the federal government or the Recovery Accountability and Transparency Board. Nothing in Leviton's use of the logo is intended to suggest anything regarding the requirements for funding under ARRA.*