



Dependable Power for Any Application

Product Datasheet

130°C Rise - Copper Windings - 480Δ Primary Volts - 208Y/120
Secondary Volts - 3Ø
C3 Transformers - Three Phase

Catalog #: TPC3533153S



PRODUCT FEATURES

- Meets or exceeds DOE CSL-3 efficiency
- UL Listed and CSA Certified
- UL Type 3R with optional Weather Shield
- Wound/Distributed core construction with copper foil
- Rated for "K" factor 13
- Available with 115°C Rise or 130°C Rise
- Covered under Acme's 25 year pro-rated warranty

BENEFITS

- 30% better performance than TP1
- Up to 40% lower losses compared to TP1 designs
- Lowest cost of ownership in transformer design

DOE

Meets or exceed U.S. DOE 10 CFR Part 431

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

Acme Electric Warranty Card

WARRANTY

www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	112.50
Primary Voltage:	480
Secondary Voltage:	208Y/120
Frequency:	60 Hz
K Factor:	13
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	130°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	41.50 (105.4)
Width (In./cm):	32.90 (83.6)
Depth (In./cm):	29.90 (75.9)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA4
Wiring Diagram:	22

PACKAGING

Ship Weight (Lbs/Kg):	1020 (462.7)
-----------------------	--------------

COMPLIANCES

DOE:	Meets or exceed U.S. DOE 10 CFR Part 431
UL Standard:	UL 1561
UL Listed:	File E12547
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf