

**3-wire fluorescent dimmers**

**(also for Hi-lume® A-Series LED drivers\*)**

**Digital fade dimmer**

Multi-location/single-pole MRF2-F6AN-DV-**XX**<sup>1</sup>  
120/277V 6A

For use with Hi-lume, Hi-lume 3D, and EcoSystem® ballasts, and Hi-lume A-Series LED drivers

For more information on Hi-lume A-Series LED drivers, visit [www.lutron.com/HilumeLED](http://www.lutron.com/HilumeLED).

Adjustable low-end trim.

Wireless switches



- Tap switch on/off
- For multi-location switching, use Maestro Wireless switch with Maestro companion switches or Pico® wireless control (see pg. 151)

**Switches**

**Digital switch\***

Multi-location/single-pole MRF2-6ANS-**XX**<sup>1</sup>  
120V 6A light or 3A fan

Rated for: incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, general purpose fans, and most non-dim LED drivers.

**Digital switches—specification grade**

Multi-location/single-pole\* MRF2-8ANS-120-**XX**<sup>1</sup>  
120V 8A light or 5.8A fan (1/4 HP motor)

Multi-location/single-pole\*\* MRF2-8S-DV-**XX**<sup>1</sup>  
120V 8A light or 3A fan or 1/16HP motor  
277V 8A light or 3A fan

Multi-location/single-pole\*\* MRF2-6ANS-277-**XX**<sup>1</sup>  
277V 8A light or 3A fan

Rated for: incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, general purpose fans, and most non-dim LED drivers.

**XX**<sup>1</sup>: Gloss color codes, see pg. 74  
(Wallplates not included. Order separately, see pg. 169)

All models must be derated if ganged unless otherwise noted, see pg. 179.

\*Requires neutral wire connection.

\*\*Minimum load required, see specification submittal.