

# GROUNDING CONNECTORS Heavy Duty for Parallel, 90° Copper Cable UC SERIES



## FEATURES

- Made of high-copper-content alloy for grounding to 1/2" - 1" ground rods and ground pipes from 1/4" - 3 1/2" in parallel or 90° position.
- Suitable for direct burial in earth and concrete.
- Nuts and lockwashers are silicon bronze.
- For use with single wire.

All dimensional data is listed in inches.

CAT. NO.	ROD SIZE	PIPE SIZE	CABLE RANGE	STD. CTN. QTY.
<b>UC-101</b>	1/2	1/4	2/0 - 4	12
<b>UC-102*</b>	1/2	1/4	250-2/0	12
<b>UC-103</b>	5/8 - 3/4	3/8	4 - 8	12
<b>UC-104</b>	5/8 - 3/4	3/8	2/0 - 4	12
<b>UC-105</b>	5/8 - 3/4	3/8	250 - 2/0	12
<b>UC-108</b>	7/8 - 1	1/2 - 3/4	2/0 - 4	12
<b>UC-109</b>	7/8 - 1	1/2 - 3/4	250 - 2/0	12
<b>UC-110*</b>	7/8 - 1	1/2 - 3/4	300-500	12
<b>UC-114</b>	-	1	2/0 - 4	6
<b>UC-115</b>	-	1	250 - 2/0	12
<b>UC-120</b>	-	1 1/4	2/0 - 4	12
<b>UC-121</b>	-	1 1/4	250 - 2/0	12
<b>UC-126</b>	-	1 1/2	2/0 - 4	12
<b>UC-127</b>	-	1 1/2	250 - 2/0	12
<b>UC-132</b>	-	2	2/0 - 4	12
<b>UC-133</b>	-	2	250 - 2/0	6
<b>UC-137</b>	-	2 1/2	2/0 - 4	6
<b>UC-138</b>	-	2 1/2	250 - 2/0	6
<b>UC-142</b>	-	3	2/0 - 4	6
<b>UC-143</b>	-	3	250 - 2/0	6
<b>UC-147</b>	-	3 1/2	2/0 - 4	3
<b>UC-148*</b>	-	3 1/2	250 - 2/0	3

\*Not UL Listed

## RATINGS



cULus  
UL Listed 467 Grounding & Bonding.

# GROUNDING CONNECTORS

## Heavy Duty for Parallel, Two & Three Conductor

### UC SERIES



#### FEATURES

- Made of high-copper-content alloy for grounding to 1/2" - 1" ground rods and ground pipes from 1/4" - 3 1/2" in parallel or 90° position.
- Suitable for direct burial in earth and concrete.
- Nuts and lockwashers are silicon bronze.
- 200 Series for use with two wires.
- 300 Series for use with three wires.



#### RATINGS



All dimensional data is listed in inches.

CAT. NO.	FIG. NO.	PIPE SIZE	CABLE RANGE	STD. CTN. QTY.
<b>UC-214</b>	1	1	2/0 - 4	6
<b>UC-215</b>	1	1	250 - 2/0	6
<b>UC-220</b>	1	1 1/4	2/0 - 4	6
<b>UC-221</b>	1	1 1/4	250 - 2/0	6
<b>UC-226</b>	1	1 1/2	2/0 - 4	6
<b>UC-227</b>	1	1 1/2	250 - 2/0	6
<b>UC-232</b>	1	2	2/0 - 4	6
<b>UC-233</b>	1	2	250 - 2/0	3
<b>UC-237</b>	1	2 1/2	2/0 - 4	3
<b>UC-238</b>	1	2 1/2	250 - 2/0	3
<b>UC-242</b>	1	3	2/0 - 4	3
<b>UC-243</b>	1	3	250 - 2/0	3
<b>UC-315</b>	2	1	250 - 2/0	6
<b>UC-320</b>	2	1 1/4	2/0 - 4	6
<b>UC-326</b>	2	1 1/2	2/0 - 4	6
<b>UC-327</b>	2	1 1/2	250 - 2/0	6
<b>UC-332</b>	2	2	2/0 - 4	6
<b>UC-333</b>	2	2	250 - 2/0	3
<b>UC-338</b>	2	2 1/2	250 - 2/0	3
<b>UC-342</b>	2	3	2/0 - 4	3
<b>UC-343</b>	2	3	250 - 2/0	3