



PAR16 GU10



PAR16 GU10



PAR20

## CAPSYLITE® PAR16 LAMPS

Suitable for use in unshielded fixtures.

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Beam Type	Class & Filament	Avg Rated Life(hrs)	Lumens CCT	CBCP	Beam Angle	MOL (in)
50	PAR16	GU10	59061	72	<b>50PAR16/HAL/GU10/FL/BL3</b>	120	18	FL	C,CC-8	3000	450 2800	800	30	2.25
			59075	72	<b>50PAR16/HAL/GU10/FL/BL</b>	120	6	FL	C,CC-8	3000	450 2800	800	30	2.25
			59024	68	<b>50PAR16/HAL/GU10/FL40</b>	120	10	FL	C,CC-2V	1000	400 2950	640	40	2.08
			59020	68	<b>50PAR16/HAL/GU10/FL/CLAM</b>	120	6	FL	C,CC-2V	1000	400 2950	640	40	2.08
60	PAR16	E26 Med	59032	69,118	<b>60PAR16/HAL/NSP10</b>	120	15	NSP	C,CC-8	2000	650 2850	5000	10	2.88
			59037	69,118	<b>60PAR16/HAL/NSP10/RP</b>	120	6	NSP	C,CC-8	2000	650 2850	5000	10	2.88
			59040	69,118,137,169	<b>60PAR16/HAL/NSP10</b>	130	15	NSP	C,CC-8	2000	650 2850	5000	10	2.88
			@ 120 volts, approximate 53 watts, 495 lumens, 4000 hours											
			59030	69,118	<b>60PAR16/HAL/NFL30</b>	120	15	NFL	C,CC-8	2000	650 2850	1300	30	2.88
			59031	69,118	<b>60PAR16/HAL/NFL30/RP</b>	120	6	NFL	C,CC-8	2000	650 2850	1300	30	2.88
75	PAR16	E26 Med	59036	69,118	<b>75PAR16/HAL/NSP10</b>	120	15	NSP	C,CC-8	2000	900 2900	7500	10	2.88
			59044	69,118,137,180	<b>75PAR16/HAL/NSP10</b>	130	15	NSP	C,CC-8	2000	900 2900	7500	10	2.88
			@ 120 volts, approximate 66 watts, 685 lumens, 4000 hours											
			59034	69,118	<b>75PAR16/HAL/NFL30</b>	120	15	NFL	C,CC-8	2000	900 2900	1900	30	2.88
			59033	69,118	<b>75PAR16/HAL/NFL30/RP</b>	120	6	NFL	C,CC-8	2000	900 2900	1900	30	2.88
59042	69,118,137,180	<b>75PAR16/HAL/NFL30</b>	130	15	NFL	C,CC-8	2000	900 2900	1900	30	2.88			
@ 120 volts, approximate 66 watts, 685 lumens, 4000 hours														

## CAPSYLITE IR® PAR20

Halogen PAR lamp with infrared reflective coating on the lamp capsule. Suitable for use in unshielded fixtures.

Watts	Bulb	Base	Product Number	Symbols & Footnotes	Ordering Abbreviation	Volts	Pkg Qty	Beam Type	Class & Filament	Avg Rated Life(hrs)	Lumens CCT	CBCP	Beam Angle	MOL (in)
40	PAR20	E26 Med	14164	43,47,118	<b>40PAR20/CAPIR/NSP10</b>	120	15	NSP	C,CC-8	4000	510 2750	4200	10	3.25
			14166	43,47,118	<b>40PAR20/CAPIR/NFL30</b>	120	15	NFL	C,CC-8	4000	510 2750	1100	30	3.25
			14130	43,47,118	<b>40PAR20/CAPIR/WFL40</b>	120	15	WFL	C,CC-8	4000	510 2750	800	40	3.25