

SYLVANIA

LEDVANCE Luminaires

Wall Pack Non-Cutoff



Product Features

The Wall Pack luminaires are environmentally preferable LED alternatives to traditional HID luminaires, offering up to 76% in energy savings. Ideal in place of traditional luminaires, or as new installations, the Wall Pack series is offered in three wattages/lumen packages for illuminating building exteriors, outdoor corridors, walkways, and stairwells.

The housing is a perfect fit for replacing existing traditional luminaires. The luminaires are available with optional photo control. LEDVANCE luminaires assure optimum light engine performance for extended service and rated life ($\geq 150,000$ hours L_{70}).

Wattage Comparison Chart

Non-Cutoff Wall Packs (UNV/347)

Traditional Source	Traditional System Wattage	LED System Wattage	Energy Savings
70W HPS	91	36/40	60%/56%
100W HPS	120	36/40	70%/70%
100W MH	130	36/40	72%/72%
70W HPS	91	50/55	45%/45%
100W HPS	120	50/55	58%/58%
100W MH	130	50/55	62%/62%
150W HPS	170	50/55	71%/68%
150W MH	188	50/55	73%/71%
175W MH	210	50/55	76%/74%
175W MH	210	75/80	64%/62%
250W MH	290	75/80	74%/72%
250W HPS	295	75/80	75%/73%

Ordering Guide


Item Number:

WALPAK	1N	/	XXX	XXX	7	XX	/	NC	/	BZ	/	X
Product Name	Generation		Wattage (UNV)	Voltage	7 = >70	Color Temp (CCT)		Optics		Color/Finish		Options
WALPAK	1N		036 = 36 Watts 050 = 50 Watts 075 = 75 Watts	UNV = 120-277V 347 = 347V		40 = 4000K* 50 = 5000K		NC = Non-cutoff Distribution		BZ = Bronze		Blank = No Options P = Photocontrol*
			Wattage (347V)									
			040 = 40 Watts 055 = 55 Watts 080 = 80 Watts									

*Available in UNV only

Catalog #	Type
Project	
Notes	
Date	
Prepared by	

Dimensions



Specifications

Weight: UNV: 13.8lbs (6.3kg) 347: 15 lbs (6.8kg)

Construction: Two-piece cast aluminum alloy housing with powder coat paint finish and a glass lens. The standard color is bronze.

LED System: LED system with a life rating of $\geq 150,000$ hours at L_{70} @25°C. Luminaire efficacy up to 120 LPW.

Electrical: Offered in 36, 50, and 75 Watts, the luminaire is designed to operate through the 120-277 Vac universal voltage range. Offered in 40, 55, and 80 Watts, the luminaire is designed to operate at the 347Vac voltage range. The LED driver is a constant current device and meets UL1310 and UL48 Class 2 with built-in over temperature protection. The power factor is $\geq 90\%$ and THD is $\leq 20\%$.

Color Characteristics: CRI >70; CCT of 4000K or 5000K.

Optics: Non-cutoff distribution with a borosilicate glass lens.

Installation: Luminaire mounts to exterior wall.

Operating Temperature: -40°F to +104°F (-40°C to +40°C).

Listings: cULus listed to UL1598 standards for wet locations.

Warranty: Standard 5-year luminaire warranty (LEDLUM001).


Note: Specifications subject to change without notice. IES files available online.



Photometric Data (UNV/347V)


WALPAK1N/036UNV750/NC

Isofootcandle Lines at 15' Mounting Height




WALPAK1N/050UNV750/NC

Isofootcandle Lines at 18' Mounting Height



WALPAK1N/075UNV750/NC

Isofootcandle Lines at 20' Mounting Height



For other mounting heights apply the following multipliers:

Mounting Height	12'	15'	18'	20'	22'
Multiplier	1.56	1.00	0.69	0.56	0.46

Mounting Height	15'	18'	20'	22'	25'
Multiplier	1.44	1.00	0.81	0.67	0.52

Mounting Height	15'	18'	20'	22'	25'
Multiplier	1.78	1.23	1.00	0.83	0.64

Ordering Information

Item Number	Ordering Abbreviation	Power (W)	Input Voltage	Color Temp CRI	(CCT)	Distribution	Total Fixture Lumens	LPW*	BUG Rating	Options
74198	WALPAK1N/036UNV740/NC/BZ	36	120-277V	>70	4000K	Type IV	3500	96	B1-U4-G3	
74199	WALPAK1N/050UNV740/NC/BZ	50	120-277V	>70	4000K	Type IV	5000	104	B1-U4-G3	
74200	WALPAK1N/075UNV740/NC/BZ	75	120-277V	>70	4000K	Type IV	8600	115	B1-U5-G5	
74201	WALPAK1N/036UNV750/NC/BZ	36	120-277V	>70	5000K	Type IV	3300	95	B1-U3-G3	
74202	WALPAK1N/050UNV750/NC/BZ	50	120-277V	>70	5000K	Type IV	5300	108	B1-U4-G3	
74203	WALPAK1N/075UNV750/NC/BZ	75	120-277V	>70	5000K	Type IV	8600	115	B1-U5-G5	
74216	WALPAK1N/036UNV740/NC/BZ/P	36	120-277V	>70	4000K	Type IV	3500	96	B1-U4-G3	Photocontrol
74217	WALPAK1N/050UNV740/NC/BZ/P	50	120-277V	>70	4000K	Type IV	5000	104	B1-U4-G3	Photocontrol
74218	WALPAK1N/075UNV740/NC/BZ/P	75	120-277V	>70	4000K	Type IV	8600	115	B1-U5-G5	Photocontrol
74219	WALPAK1N/036UNV750/NC/BZ/P	36	120-277V	>70	5000K	Type IV	3300	95	B1-U3-G3	Photocontrol
74220	WALPAK1N/050UNV750/NC/BZ/P	50	120-277V	>70	5000K	Type IV	5300	108	B1-U4-G3	Photocontrol
74221	WALPAK1N/075UNV750/NC/BZ/P	75	120-277V	>70	5000K	Type IV	8600	115	B1-U5-G5	Photocontrol
72996	WALPAK1N/040347750/NC/BZ	40	347	>70	5000K	Cutoff	4300	102	B1-U4-G3	
72997	WALPAK1N/055347750/NC/BZ	55	347	>70	5000K	Cutoff	6300	110	B1-U4-G4	
72998	WALPAK1N/080347750/NC/BZ	80	347	>70	5000K	Cutoff	9400	120	B1-U5-G5	

*LPW per LM79 report.
For further information and to learn more about utility rebates, contact your local SYLVANIA sales representative.

LEDVANCE LLC
200 Ballardvale Street
Wilmington, MA 01887 USA
Phone 1-800-LIGHTBULB (1-800-544-4828)
www.sylvania.com

SYLVANIA and LEDVANCE are registered trademarks.
All other trademarks are those of their respective owners.
Product Licensee of Trademark SYLVANIA in General Lighting.
Specifications subject to change without notice.

[/sylvania](#) [/sylvania](#)

