

## Specification Data

Fixture Description:	Type
Project/Job:	
SYLVANIA lamp:	
SYLVANIA ballast:	
Notes:	

### Ordering Information

Item Number	Ordering Abbreviation	Watts	Bulb	Base	Nominal Length	Rated Life		Programmed Rapid Start		Initial Lumens	Mean Lumens	CCT	CRI
						Instant Start 3 hrs/ start	12 hrs/ start	3 hrs/ start	12 hrs/ start				
<b>OCTRON® and OCTRON CURVALUME®</b>													
22271	F017/835/XP/ECO3/SL	17	T8	Medium Bi-Pin	24"	24,000	40,000	40,000	42,000	1350	1283	3500K	85
22378	F025/830/XP/ECO3/SL	25	T8	Medium Bi-Pin	36"	24,000	40,000	40,000	42,000	2107	1936	3000K	82
22273	F025/835/XP/ECO3/SL	25	T8	Medium Bi-Pin	36"	24,000	40,000	40,000	42,000	2130	2024	3500K	85
22279	F028/835/XP/SS/ECO3/SL	28	T8	Medium Bi-Pin	48"	24,000	40,000	40,000	42,000	2670	2537	3500K	85
21948	F028/841/XP/SS/ECO3/SL	28	T8	Medium Bi-Pin	48"	24,000	40,000	40,000	42,000	2670	2537	4100K	85
22275	F032/730/ECO/SL	32	T8	Medium Bi-Pin	48"	24,000	28,000	30,000	35,000	2750	2475	3000K	78
21678	F032/735/ECO/SL	32	T8	Medium Bi-Pin	48"	24,000	28,000	30,000	35,000	2716	2444	3500K	78
21547	F032/741/ECO/SL	32	T8	Medium Bi-Pin	48"	24,000	28,000	30,000	35,000	2716	2444	4100K	78
22387	F032/841/XPS/ECO3/SL	32	T8	Medium Bi-Pin	48"	24,000	40,000	40,000	42,000	3038	2886	4100K	85
22278	F032/841/XP/ECO3/SL	32	T8	Medium Bi-Pin	48"	24,000	40,000	40,000	42,000	2940	2793	4100K	85
22389	F032/850/XPS/ECO3/SL	32	T8	Medium Bi-Pin	48"	24,000	40,000	40,000	42,000	3038	2886	5000K	81
22142	F032/850/XP/ECO/SL	32	T8	Medium Bi-Pin	48"	24,000	40,000	40,000	42,000	2940	2793	5000K	85
22281	F040/835/XP/ECO3/SL	40	T8	Medium Bi-Pin	60"	24,000	40,000	40,000	42,000	3675	3491	3500K	85
21509	F096/841/ECO/SL	59	T8	Single Pin	96"	24,000	30,000			5782	5319	4100K	82
<b>PENTRON®</b>													
Item Number	Ordering Abbreviation	Watts	Bulb	Base	Nominal Length	Rated Life		Initial Lumens	Mean Lumens	CCT	CRI		
						Programmed Rapid Start 3 hrs/ start	12 hrs/ start						
21027	FP21/835/ECO/SL	21	T5	Miniature Bi-Pin	36"	20,000		1860	1730	3500K	85		
21034	FP28/835/ECO/SL	28	T5	Miniature Bi-Pin	48"	25,000		2550	2372	3500K	85		
20051	FP54/50W/841/HO/SS/ECO/SL	50	T5	Miniature Bi-Pin	48"	30,000	40,000	4850	4510	4100K	85		
20052	FP54/50W/850/HO/SS/ECO/SL	50	T5	Miniature Bi-Pin	48"	30,000	40,000	4753	4420	5000K	85		
21020	FP54/835/HO/ECO/SL	54	T5	Miniature Bi-Pin	48"	30,000	40,000	4850	4510	3500K	85		
21021	FP54/841/HO/ECO/SL	54	T5	Miniature Bi-Pin	48"	30,000	40,000	4850	4510	4100K	85		
21022	FP54/850/HO/ECO/SL	54	T5	Miniature Bi-Pin	48"	30,000	40,000	4753	4420	5000K	85		
<b>T12</b>													
Item Number	Ordering Abbreviation	Watts	Bulb	Base	Nominal Length	Rated Life		Initial Lumens	Mean Lumens	CCT	CRI		
						Rapid Start 3 hrs/ start							
24396	F34CW/SS/SL	34	T12	Medium Bi-Pin	48"	20,000		2570	2313	4200K	60		
24740	F40/D835/ECO/SL	40	T12	Medium Bi-Pin	48"	20,000		3230	2907	3500K	80		
25283	F72T12/D835/HO/SL	85	T12	Recessed DC	72"	10,000		6620	6090	3500K	80		
<b>T12 SUPERSAVER®</b>													
29555	F96T12/CW/SS/SL	60	T12	Single Pin	96"	12,000		5140	4420	4200K	60		