

HSTTV Heat Shrink on 100 Foot Reels

- Applications include insulating and protecting wires and cables
- Fast shrink time
- Voltage: 600 V
- Shrink ratio: 2:1
- Flammability: Meets UL 224 VW-1

- UL Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 3
- Temperature range: -67°F to 275°F (-55°C to 135°C)
- For dry locations
- Material: Black Cross-linked Polyolefin



Part Number	Nominal Diameter		Min. Expanded I.D.		Max. Recovered I.D.		Nominal Recovered Wall Thickness		Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm		
HSTTV05-C	0.046	1.2	0.046	1.2	0.023	0.6	0.016	0.4	1	10
HSTTV06-C	0.063	1.6	0.063	1.6	0.031	0.8	0.017	0.4	1	10
HSTTV09-C	0.093	2.4	0.093	2.4	0.046	1.2	0.020	0.5	1	10
HSTTV12-C	0.125	3.2	0.125	3.2	0.062	1.6	0.020	0.5	1	10
HSTTV19-C	0.187	4.8	0.187	4.8	0.093	2.4	0.020	0.5	1	10
HSTTV25-C	0.250	6.4	0.250	6.4	0.125	3.2	0.025	0.6	1	10
HSTTV38-C	0.375	9.5	0.375	9.5	0.187	4.8	0.025	0.6	1	10
HSTTV50-C	0.500	12.7	0.500	12.7	0.250	6.4	0.025	0.6	1	10
HSTTV75-C	0.750	19.1	0.750	19.1	0.375	9.5	0.030	0.8	1	10
HSTTV100-C	1.00	25.4	1.00	25.4	0.500	12.7	0.035	0.9	1	2
HSTTV100-C5*	1.00	25.4	1.00	25.4	0.500	12.7	0.035	0.9	1	2
HSTTV150-C	1.50	38.1	1.50	38.1	0.750	19.1	0.040	1.0	1	2

*Green.

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index

PANDUIT® ELECTRICAL SOLUTIONS

A. System Overview	Part Number	Page Number	Part Number	Page Number	Part Number	Page Number
B1. Cable Ties	HSTTT93-48-5	C3.34	HSTTV50-T	C3.30	HVMPPM32-C0	B2.21, B1.62
	HSTTV05-48-Q	C3.28	HSTTV50-T2	C3.30	HVTM-06-C0	B2.11
	HSTTV05-48-TL	C3.28	HSTTV50-T4	C3.30	HVTM3S10-C0	B1.62
	HSTTV05-C	C3.29	HSTTV50-T6	C3.30	HWS2819-C	B2.43
	HSTTV05-M	C3.30	HSTTV50-Y	C3.31	I	
B2. Cable Accessories	HSTTV05-M2	C3.30	HSTTV75-48-5	C3.28	ICF10IW-X	C2.61
	HSTTV05-M4	C3.30	HSTTV75-48-CQ	C3.28	ICF3IW-E	C2.61
	HSTTV05-M6	C3.30	HSTTV75-C	C3.29	ICF5IW-E	C2.61
	HSTTV05-Q	C3.31	HSTTV75-Q	C3.31	ICFC10IW-X	C2.62
	HSTTV05-Y	C3.31	HSTTV75-T	C3.30	ICFC3IW-X	C2.62
B3. Stainless Steel Ties	HSTTV06-48-Q	C3.28	HSTTV75-T2	C3.30	ICFC5IW-X	C2.62
	HSTTV06-48-TL	C3.28	HSTTV75-T4	C3.30	ICFX10IW-X	C2.57, C2.63
	HSTTV06-C	C3.29	HSTTV75-T6	C3.30	ICFX3IW-X	C2.63
	HSTTV06-M	C3.30	HSTTV75-Y	C3.31	ICFX5IW-X	C2.63
	HSTTV06-M2	C3.30	HSTTVVA100-48-5	C3.35	ILT2S-C	B1.61
C1. Wiring Duct	HSTTV06-M4	C3.30	HSTTVVA100-Y	C3.36	ILT2S-C0	B1.61
	HSTTV06-M6	C3.30	HSTTVVA12-48-Q	C3.35	ILT3S-C	B1.61
	HSTTV06-Q	C3.31	HSTTVVA19-48-Q	C3.35	ILT3S-C0	B1.61
	HSTTV06-Y	C3.31	HSTTVVA19-Y	C3.36	ILT4LH-TL	B1.61
	HSTTV09-48-Q	C3.28	HSTTVVA25-48-Q	C3.35	ILT4LH-TL0	B1.61
C2. Surface Raceway	HSTTV09-48-TL	C3.28	HSTTVVA25-Y	C3.36	ILT4S-C	B1.61
	HSTTV09-C	C3.29	HSTTVVA38-48-Q	C3.35	ILT4S-C0	B1.61
	HSTTV09-M	C3.30	HSTTVVA38-Y	C3.36	ILT6LH-C	B1.61
	HSTTV09-M2	C3.30	HSTTVVA50-48-5	C3.35	ILT6LH-C0	B1.61
	HSTTV09-M4	C3.30	HSTTVVA50-Y	C3.36	IT9100-C0	B1.63
C3. Abrasion Protection	HSTTV09-M6	C3.30	HSTTVVA75-48-5	C3.35	IT9100-CUV16B	B1.63
	HSTTV09-Q	C3.31	HSTTVVA75-Y	C3.36	IT9100-CUV2	B1.63
	HSTTV09-Y	C3.31	HT2-BLU	E5.33	IT9100-CUV4Y	B1.63
	HSTTV100-48-5	C3.28	HT2-GRN	E5.33	IT9100-CUV6	B1.63
	HSTTV100-48-LQ	C3.28	HT2-ORN	E5.33	IT9100-CUV6A	B1.63
C4. Cable Management	HSTTV100-C	C3.29	HT2-RED	E5.33	IT9100-CUV7A	B1.63
	HSTTV100-C5	C3.29	HT2-WHT	E5.33	IT9100-CUV8	B1.63
	HSTTV100-Q	C3.31	HT2-YEL	E5.33	IT9115-C0	B1.63
	HSTTV100-T2	C3.30	HT2S-BLK-YEL	E5.33	IT9115-CUV11	B1.63
	HSTTV100-Y	C3.31	HT2S-RED-WHT	E5.33	IT9115-CUV16B	B1.63
D1. Terminals	HSTTV12-48-Q	C3.28	HT3S-BLK-YEL	E5.33	IT9115-CUV18	B1.63
	HSTTV12-48-TL	C3.28	HT3S-RED-WHT	E5.33	IT9115-CUV2	B1.63
	HSTTV12-C	C3.29	HTB3-C-M	E5.36	IT9115-CUV2A	B1.63
	HSTTV12-M	C3.30	HTB3-DNE-M	E5.36	IT9115-CUV4A	B1.63
	HSTTV12-M2	C3.30	HTB3-HV-M	E5.36	IT9115-CUV4Y	B1.63
D2. Power Connectors	HSTTV12-M4	C3.30	HTCT2-2-1	D3.14	IT9115-CUV5A	B1.63
	HSTTV12-Q	C3.31	HTCT250-2-1	D3.14	IT9115-CUV5B	B1.63
	HSTTV12-Y	C3.31	HTCT250-250-1	D3.14	IT9115-CUV6	B1.63
	HSTTV150-48-5	C3.28	HTCT6X-6X-1	D3.14	IT9115-CUV6A	B1.63
	HSTTV150-C	C3.29	HTDU2B-W	E5.35	IT9115-CUV6B	B1.63
D3. Grounding Connectors	HSTTV19-48-Q	C3.28	HTDU20-FO	E5.35	IT9115-CUV7A	B1.63
	HSTTV19-48-TL	C3.28	HTDU20-T	E5.35	IT9115-CUV8	B1.63
	HSTTV19-C	C3.29	HTDU2R-E	E5.35	IT940-C0	B1.63
	HSTTV19-M	C3.30	HTDU30-FO	E5.35	IT965-C0	B1.63
	HSTTV19-M2	C3.30	HTDU30-T	E5.35	J	
E1. Labeling Systems	HSTTV19-M4	C3.30	HTDU3R-E	E5.35	J214-312-T	D1.68
	HSTTV19-M6	C3.30	HTDU60-FO	E5.35	J216-410-L	D1.68
	HSTTV19-Q	C3.31	HTDU60-T	E5.35	J318-412-T	D1.68
	HSTTV19-Y	C3.31	HTDU6R-E	E5.35	JB1DIW-A	C2.39
	HSTTV25-48-Q	C3.28	HTMT	B3.15	JB1FSIW-A	C2.34, C2.39
E2. Labels	HSTTV25-48-TL	C3.28	HTU3G-T-M	E5.35	JB1IW-A	C2.39
	HSTTV25-C	C3.29	HTU30-FO-M	E5.35	JBA-X	C2.39
	HSTTV25-D	C3.30	HTU30-T-M	E5.35	JBD1	C2.41
	HSTTV25-D2	C3.30	HTU3R-E-M	E5.35	JBD2	C2.41
	HSTTV25-D4	C3.30	HTU3Y-E-M	E5.35	JBP1DIW	C2.40
E3. Pre-Printed & Write-On Markers	HSTTV25-D6	C3.30	HTU60-FO	E5.35	JBP1EIW	C2.40
	HSTTV25-Q	C3.31	HTU60-T	E5.35	JBP1FSIW	C2.34, C2.41
	HSTTV25-Y	C3.31	HTU60-TV	E5.35	JBP1IW	C2.40
	HSTTV38-48-Q	C3.28	HTU6R-E	E5.35	JBP1IW	C2.40
	HSTTV38-48-TL	C3.28	HTU6Y-E	E5.35	JBP1MD20IW	C2.41, C2.43
E4. Permanent Identification	HSTTV38-C	C3.29	HTU6Y-G	E5.35	JBP1MR20IW	C2.41, C2.43
	HSTTV38-Q	C3.31	HTWC2-2-1	D3.15	JBP2DIW	C2.39, C2.40
	HSTTV38-T	C3.30	HTWC250-2-1	D3.15	JBP2FSIW	C2.34, C2.41
	HSTTV38-T2	C3.30	HTWC250-250-1	D3.15	JBP2IW	C2.39, C2.40
	HSTTV38-T4	C3.30	HTWC6X-6X-1	D3.15	JBP2SIW	C2.41
E5. Lockout/Tagout & Safety Solutions	HSTTV38-T6	C3.30	HV9100-C	B1.64	JBX3510IW-A	C2.39
	HSTTV38-Y	C3.31	HV9100-C0	B1.62	JMCB-X	C4.8
	HSTTV50-48-Q	C3.28	HV9150-C0	B1.62	JMCMB25-1-X	C4.8
	HSTTV50-48-T	C3.28	HV9250-C0	B1.62		
	HSTTV50-C	C3.29	HV965-C0	B1.62		
F. Index	HSTTV50-Q	C3.31				