

A. System Overview

## Thermal Transfer Military Grade Heat Shrink Labels

- Labels offer crisp, clear legends with superior legibility
- Meets UL Standard 224 for flammability and AMS-DTL-23053/5C (Class 1 and Class 3)
- Will meet MIL-M-81531, MIL-STD202F, and MIL-STD-883E when printed with RMH4BL or RHH4BL-S ribbons
- Shrink ratio 3:1
- Pre-cut flattened polyolefin is both thermal transfer and dot matrix printable and supplied roll mounted on plastic carrier
- Panduit labeling software packages include all label formats for quick and easy label production

B1. Cable Ties


B2. Cable Accessories



B3. Stainless Steel Ties

C1. Wiring Duct

## Part Number System for Heat Shrink Labels



C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

### Material/Print Method Selection Guide

Material	Print Method	Temperature Range	Features
Heat Shrinkable Polyolefin, White (H1) Yellow (H2) Black (H3) Red (H4)	Thermal Transfer (T)	-67°F to 275°F (-55°C to 135°C)	Durable flattened polyolefin, high quality heat shrink wire/cable labels.

D2. Power Connectors

D3. Grounding Connectors

Part Number	Part Description	Width		Length		Min. Cable O.D.		Max. Cable O.D.		Std. Pkg. Qty.
		In.	mm	In.	mm	In.	mm	In.	mm	
<b>H050X025H1T*</b>	White, 1/8" diameter polyolefin, 2000/roll.	0.50	12.7	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H050X025H1T-B</b>	White, 1/8" diameter polyolefin, 10000/roll.	0.50	12.7	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H050X034H1T*</b>	White, 3/16" diameter polyolefin, 2000/roll.	0.50	12.7	0.34	8.6	0.06	1.5	0.19	4.8	1
<b>H050X034H1T-B</b>	White, 3/16" diameter polyolefin, 10000/roll.	0.50	12.7	0.34	8.6	0.06	1.5	0.19	4.8	1
<b>H050X044H1T*</b>	White, 1/4" diameter polyolefin, 2000/roll.	0.50	12.7	0.44	11.2	0.08	2.0	0.25	6.4	1
<b>H050X044H1T-B</b>	White, 1/4" diameter polyolefin, 10000/roll.	0.50	12.7	0.44	11.2	0.08	2.0	0.25	6.4	1
<b>H050X064H1T*</b>	White, 3/8" diameter polyolefin, 2000/roll.	0.50	12.7	0.64	16.3	0.13	3.3	0.38	9.7	1
<b>H050X064H1T-B</b>	White, 3/8" diameter polyolefin, 10000/roll.	0.50	12.7	0.64	16.3	0.13	3.3	0.38	9.7	1
<b>H075X025H1T*</b>	White, 1/8" diameter polyolefin, 1000/roll.	0.75	19.1	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H075X034H1T*</b>	White, 1/8" diameter polyolefin, 1000/roll.	0.75	19.1	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H075X044H1T*</b>	White, 1/8" diameter polyolefin, 5000/roll.	0.75	19.1	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H100X025H1T*</b>	White, 1/8" diameter polyolefin, 1000/roll.	1.00	25.4	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H100X025H1T-B</b>	White, 1/8" diameter polyolefin, 5000/roll.	1.00	25.4	0.25	6.4	0.04	1.0	0.13	3.3	1
<b>H100X034H1T*</b>	White, 3/16" diameter polyolefin, 1000/roll.	1.00	25.4	0.34	8.6	0.06	1.5	0.19	4.8	1
<b>H100X034H1T-B</b>	White, 3/16" diameter polyolefin, 5000/roll.	1.00	25.4	0.34	8.6	0.06	1.5	0.19	4.8	1
<b>H100X044H1T*</b>	White, 1/4" diameter polyolefin, 1000/roll.	1.00	25.4	0.44	11.2	0.08	2.0	0.25	6.4	1
<b>H100X044H1T-B</b>	White, 1/4" diameter polyolefin, 5000/roll.	1.00	25.4	0.44	11.2	0.08	2.0	0.25	6.4	1
<b>H100X064H1T*</b>	White, 3/8" diameter polyolefin, 1000/roll.	1.00	25.4	0.64	16.3	0.13	3.3	0.38	9.7	1
<b>H100X064H1T-B</b>	White, 3/8" diameter polyolefin, 5000/roll.	1.00	25.4	0.64	16.3	0.13	3.3	0.38	9.7	1

\*Other colors available, replace H1T with H2T (Yellow), H3T (Black), and H4T (Red).  
Order number of rolls required.

F. Index

# PANDUIT® ELECTRICAL SOLUTIONS

A. System Overview	Part Number	Page Number	Part Number	Page Number	Part Number	Page Number	
B1. Cable Ties	<b>GPQC15-1/0</b> .....	<b>D3.5</b>	H200X025H1T-B .....	E2.13	HL8-1-X .....	D2.130	
	<b>GPQC17-1/0</b> .....	<b>D3.5</b>	H200X034H1T .....	E2.13	HL8-2-X .....	D2.132	
	<b>GPQC20-1/0</b> .....	<b>D3.5</b>	H200X034H1T-2 .....	E2.15	HL8-2N-X .....	D2.133	
	GS2B .....	B1.111	H200X034H1T-2-B .....	E2.15	HLA13-1-90-5 .....	D2.131	
	GS4EH .....	B1.111	H200X034H1T-B .....	E2.13	HLA21-1-90-5 .....	D2.131	
	GS4H .....	B1.111	H200X044H1T .....	E2.13	HLA4-1-90-X .....	D2.131	
	GS4MT .....	B3.14	H200X044H1T-2 .....	E2.15	HLA8-1-90-X .....	D2.131	
	GTH .....	B1.111	H200X044H1T-2-B .....	E2.15	HLB2S-C0 .....	B1.87	
	GTS .....	B1.111	H200X044H1T-B .....	E2.13	HLB4-1-X .....	D2.130	
	GTSL .....	B1.111	H200X064H1T .....	E2.13	HLM-15R0 .....	B1.87	
B3. Stainless Steel Ties	GU-13-3 .....	D3.26	H200X064H1T-2 .....	E2.15	HLS-15R0 .....	B1.87	
	GU-2-X .....	D3.26	H200X064H1T-2-B .....	E2.15	HLS-75R0 .....	B1.87	
	GU-4-X .....	D3.26	H200X064H1T-B .....	E2.13	HLS1.5S-X0 .....	B1.87	
B2. Cable Accessories	<b>GUBC500-6</b> .....	<b>D3.10</b>	H200X084H1T .....	E2.13	HLS-15R0 .....	B1.87	
	<b>H</b>						
	C1. Wiring Duct	H000X025H1C .....	E1.8	H200X084H1T-2 .....	E2.15	HLS3S-X0 .....	B1.87
		H000X025H2C .....	E1.8	H200X084H1T-2-B .....	E2.15	HLS5S-X0 .....	B1.87
		H000X034H1C .....	E1.8	H200X084H2T .....	E2.13	HLS-75R0 .....	B1.87
	C2. Surface Raceway	H000X034H2C .....	E1.8	H200X122H1T-2 .....	E2.15	HLSP1.5S-X0 .....	B1.88
		H000X044H1C .....	E1.8	H200X165H1T .....	E2.13	HLSP1.5S-X12 .....	B1.88
		H000X044H2C .....	E1.8	H200X165H1T-2 .....	E2.15	HLSP3S-X0 .....	B1.88
	C3. Abrasion Protection	H000X064H1C .....	E1.8	H200X165H2T .....	E2.14	HLSP3S-X12 .....	B1.88
		H000X064H2C .....	E1.8	H2L13-2N-2 .....	D2.134	HLSP5S-X0 .....	B1.88
H000X084H1C .....		E1.8	H2L21-2N-2 .....	D2.134	HLSP5S-X12 .....	B1.88	
H000X084H2C .....		E1.8	H2L30-2N-1 .....	D2.134	HLT2I-X0 .....	B1.87	
H050X025H1T .....		E2.12	H2L4-2N-X .....	D2.134	HLT3I-X0 .....	B1.87	
H050X025H1T-B .....		E2.12	H2L8-2N-2 .....	D2.134	HLTP2I-X0 .....	B1.88	
H050X044H1T .....		E2.12	H2X2LG6 .....	C1.11	HLTP2I-X12 .....	B1.88	
H050X044H1T-B .....		E2.12	H2X3LG6 .....	C1.11	HLTP3I-X0 .....	B1.88	
H050X064H1T .....		E2.12	H2X4LG6 .....	C1.11	HLTP3I-X12 .....	B1.88	
H050X064H1T-B .....		E2.12	H3X3LG6 .....	C1.11	<b>HLWM1.5S-X0</b> .....	<b>B1.91</b>	
C4. Cable Management	H075X025H1T .....	E2.12	H3X4LG6 .....	C1.11	<b>HLWM3S-X0</b> .....	<b>B1.91</b>	
	H075X025H1T-B .....	E2.12	H4X4LG6 .....	C1.11	HN1.5X2LG6 .....	C1.11	
	H075X034H1T .....	E2.12	HB2SP19-X .....	B2.51	HN1.5X3LG6 .....	C1.11	
	H075X034H1T-B .....	E2.12	HB2SP25-X .....	B2.51	HN2X2LG6 .....	C1.11	
	H075X044H1T .....	E2.12	HBN.75-T .....	B2.49	HN2X3LG6 .....	C1.11	
	H075X044H1T-B .....	E2.12	HBN1-T .....	B2.49	HN2X4LG6 .....	C1.11	
	H1.5X2LG6 .....	C1.11	HBN1.5-T .....	B2.49	HN3X3LG6 .....	C1.11	
	H1.5X3LG6 .....	C1.11	HBN2-T .....	B2.49	HN3X4LG6 .....	C1.11	
	H100X025H1C .....	E1.9	HBN2.5-T .....	B2.49	HN4X4LG6 .....	C1.11	
	H100X025H1T .....	E2.13	HBN3-T .....	B2.49	HS1.5X2LG6NM .....	C1.11	
D1. Terminals	H100X025H1T-2 .....	E2.14	HBN4-T .....	B2.49	HS1.5X3LG6NM .....	C1.11	
	H100X025H1T-2-B .....	E2.14	HBUA-X .....	B2.51	HS2X2LG6NM .....	C1.11	
	H100X025H1T-B .....	E2.12	HC1.5LG6 .....	C1.11	HS2X3LG6NM .....	C1.11	
	H100X025H2C .....	E1.9	HC2LG6 .....	C1.11	HS2X4LG6NM .....	C1.11	
	H100X034H1C .....	E1.9	HC3LG6 .....	C1.11	HS3X3LG6NM .....	C1.11	
	H100X034H1T .....	E2.12	HC4LG6 .....	C1.11	HS3X4LG6NM .....	C1.11	
	H100X034H1T-2 .....	E2.14	HC13-3 .....	D2.135	HS4X4LG6NM .....	C1.11	
	H100X034H1T-2-B .....	E2.14	HC21-1 .....	D2.135	HSC.25-L .....	B2.41	
	H100X034H1T-B .....	E2.14	HC30-1 .....	D2.135	HSC.25-L100 .....	B2.41	
	H100X034H2C .....	E1.9	HC4-3 .....	D2.135	HSEC0.5-X .....	C3.39	
D2. Power Connectors	H100X044H1C .....	E1.9	HC50-1 .....	D2.135	HSEC0.8-X .....	C3.39	
	H100X044H1T .....	E2.12	HC8-3 .....	D2.135	HSEC1.0-X .....	C3.39	
	H100X044H1T-2 .....	E2.14	HCME04Y09-C30 .....	B2.45	HSEC1.5-5 .....	C3.39	
	H100X044H1T-2-B .....	E2.14	HCME06A12-C130 .....	B2.45	HSEC2.0-5 .....	C3.39	
	H100X044H1T-B .....	E2.12	HCME06Y12-C30 .....	B2.45	HSEC4.0-2 .....	C3.39	
	H100X044H2C .....	E1.9	HCMP06B12-C20 .....	B2.44	HSECFR0.5-XY .....	C3.39	
	H100X064H1C .....	E1.9	HCMP06C12-C20 .....	B2.44	HSECFR0.8-XY .....	C3.39	
	H100X064H1T .....	E2.12	HHL13-2N-5 .....	D2.133	HSECFR1.0-XY .....	C3.39	
	H100X064H1T-2 .....	E2.14	HHL21-2N-5 .....	D2.133	HSECFR1.5-5Y .....	C3.39	
	H100X064H1T-2-B .....	E2.14	HHL30-22N-1 .....	D2.133	HSECFR2.0-5Y .....	C3.39	
D3. Grounding Connectors	H100X064H1T-B .....	E2.12	HHL8-2N-X .....	D2.133	HSG-115V-650 .....	C3.40	
	H100X064H2C .....	E1.9	HKBS .....	C3.16	HSG-A1 .....	C3.40, E2.15	
	H100X084H1C .....	E1.9	HL1-2-25-X .....	D2.132	HSG-A2 .....	C3.40, E2.15	
	H100X084H1T .....	E2.13	HL1-25-X .....	D2.130	HSG-A4 .....	C3.40, E2.15	
	H100X084H1T-2 .....	E2.14	HL13-1-5 .....	D2.130	HSG-P1 .....	C3.40, E2.15	
	H100X084H1T-2-B .....	E2.14	HL13-2-5 .....	D2.132	HSG-P2 .....	C3.40, E2.15	
	H100X084H1T-B .....	E2.14	HL13-2N-5 .....	D2.133	HSG-P3 .....	C3.40, E2.15	
	H100X084H2C .....	E1.9	HL21-1-5 .....	D2.130	HSG-P7 .....	C3.40, E2.15	
	H100X122H1T-2 .....	E2.14	HL21-2-5 .....	D2.132	HST0.4-3-Q2Y .....	C3.38	
	H100X165H1T .....	E2.13	HL21-2N-5 .....	D2.133	HST0.4-3-QY .....	C3.38	
E1. Labeling Systems	H100X165H1T-2 .....	E2.14	HL30-1-2 .....	D2.130	HST0.4-48-5-2Y .....	C3.38	
	H100X044H1T .....	E2.12	HL30-2-2 .....	D2.132	HST0.4-48-5Y .....	C3.38	
	H100X044H1T-2 .....	E2.14	HL30-2N-2 .....	D2.133	HST0.4-6-3Y .....	C3.38	
	H100X044H1T-2-B .....	E2.14	HL4-1-X .....	D2.130	HST0.4-6-X2Y .....	C3.38	
	H100X044H1T-B .....	E2.12	HL4-2-X .....	D2.132	HST0.4-6-XY .....	C3.38	
	H100X064H1C .....	E1.9	HL50-1-2 .....	D2.130	HST0.8-12-5-2Y .....	C3.38	
	H100X064H1T .....	E2.12	HL50-2-2 .....	D2.132	HST0.8-12-5Y .....	C3.38	
	H100X064H1T-2 .....	E2.14					
	H100X064H1T-2-B .....	E2.14					
	H100X064H2C .....	E1.9					
E2. Labels	H100X084H1C .....	E1.9					
	H100X084H1T .....	E2.13					
	H100X084H1T-2 .....	E2.14					
	H100X084H1T-2-B .....	E2.14					
	H100X084H1T-B .....	E2.14					
	H100X084H2C .....	E1.9					
	H100X122H1T-2 .....	E2.14					
	H100X165H1T .....	E2.13					
	H100X165H1T-2 .....	E2.14					
	H150X025H1T .....	E2.14					
E3. Pre-Printed & Write-On Markers	H150X034H1T .....	E2.13					
	H150X044H1T .....	E2.14					
	H200X025H1T .....	E2.13					
	H200X025H1T-2 .....	E2.15					
	H200X034H1T .....	E2.13					
	H200X034H1T-2 .....	E2.15					
	H200X044H1T .....	E2.13					
	H200X044H1T-2 .....	E2.15					
	H200X064H1T .....	E2.13					
	H200X064H1T-2 .....	E2.15					
E4. Permanent Identification	H200X084H1T .....	E2.13					
	H200X084H1T-2 .....	E2.15					
	H200X084H1T-B .....	E2.13					
	H200X084H1T-2-B .....	E2.15					
	H200X122H1T-2 .....	E2.14					
	H200X165H1T .....	E2.13					
	H200X165H1T-2 .....	E2.14					
	H200X165H1T-2-B .....	E2.14					
	H200X25H1T-2-B .....	E2.15					
E5. Lockout/Tagout & Safety Solutions							
F. Index							