

Item Number	Ordering Abbreviation	ENERGY STAR®	Wattage (W)	Lumens	Beam Angle	CBCP (cd)	Color	CRI	Lifetime (Hrs)	Replacing
PAR30LN										
72526	LED13PAR30LN/DIM/850/FL40 [RP]	N/A	13	800	40°	1690	5000K	86	25,000	50W Halogen
78431	LED13PAR30LN/DIM/827/NFL25	Yes	13	790	25°	3400	2700K	82	25,000	50W Halogen
78655*	LED15PAR30LN/DIM/827/NFL25	Yes	15	700	25°	2910	2700K	84	25,000	50W Halogen
78432	LED13PAR30LN/DIM/827/FL40	Yes	13	790	40°	1400	2700K	82	25,000	50W Halogen
78656*	LED15PAR30LN/DIM/827/FL40	Yes	15	700	40°	1420	2700K	84	25,000	50W Halogen
78429	LED13PAR30LN/DIM/830/NFL25	Yes	13	820	25°	3600	3000K	82	25,000	50W Halogen
78638*	LED15PAR30LN/DIM/830/NFL25	Yes	15	770	25°	2900	3000K	87	50,000	50W Halogen
78430	LED13PAR30LN/DIM/830/FL40	Yes	13	820	40°	1450	3000K	82	25,000	50W Halogen
78639*	LED15PAR30LN/DIM/830/FL40	Yes	15	770	40°	1300	3000K	87	50,000	50W Halogen
78720	LED17PAR30LN/DIM/830/WSP20	N/A	17	1200	20°	5700	3000K	81	25,000	75W Halogen
78746	LED17PAR30LN/DIM/P/930/NFL25	Yes	17	970	25°	3400	3000K	95	50,000	75W Halogen
78742	LED17PAR30LN/GU24/DIM/P/930/NFL25	Yes	17	970	25°	3400	3000K	95	50,000	75W Halogen
78758	LED17PAR30LN/DIM/P/930/FL40	Yes	17	970	40°	1600	3000K	95	50,000	75W Halogen
78804*	LED18PAR30LN/DIM/830/NFL25	Yes	18	950	25°	3810	3000K	85	25,000	75W Halogen
78805*	LED18PAR30LN/DIM/830/FL40	No	18	950	40°	1500	3000K	85	25,000	75W Halogen



PAR20										
72527	LED7PAR20/DIM/850/FL36 [RP]	N/A	7	430	30°	1000	5000K	86	25,000	50W Halogen
78425	LED8PAR20/DIM/827/NFL25	Yes	8	450	25°	1700	2700K	82	25,000	50W Halogen
78653*	LED8PAR20/DIM/827/NFL25	Yes	8	320	25°	1150	2700K	85	25,000	35W Halogen
78426	LED8PAR20/DIM/827/FL36	Yes	8	450	36°	900	2700K	82	25,000	50W Halogen
78654*	LED8PAR20/DIM/827/FL36	Yes	8	320	36°	670	2700K	85	25,000	35W Halogen
78427	LED8PAR20/DIM/H/830/NFL25	Yes	8	450	25°	1900	3000K	82	25,000	50W Halogen
78802*	LED8PAR20/DIM/H/830/NFL25	Yes	8	400	25°	2000	3000K	85	25,000	35W Halogen
78428	LED8PAR20/DIM/H/830/FL36	Yes	8	450	36°	1000	3000K	82	25,000	50W Halogen
78803*	LED8PAR20/DIM/H/830/FL36	Yes	8	400	36°	675	3000K	85	25,000	35W Halogen
78963	LED10PAR20/DIM/825/WSP20/SG	N/A	10	550	20°	2200	2500K	80	25,000	50W Halogen
78748	LED10PAR20/DIM/P/930/FL30	Yes	10	550	30°	1600	3000K	95	25,000	50W Halogen
78744	LED10PAR20/GU24/DIM/P/930/FL30	Yes	10	550	30°	1600	3000K	95	25,000	50W Halogen



PAR16										
78964	LED7PAR16/DIM/GU10/830/FL36	Yes	7	350	36°	650	3000K	84	25,000	35W Halogen
78834*	LED5.5PAR16/GU10/830/NFL25	Yes	5.5	300	30°	460	3000K	84	25,000	35W Halogen
78965	LED7PAR16/DIM/830/FL36	Yes	7	350	36°	650	3000K	84	25,000	35W Halogen
78831*	LED5.5PAR16/830/NFL25	Yes	5.5	300	30°	460	3000K	80	50,000	35W Halogen
72546	LED8PAR16/DIM/930/FL36P [RP]	O/T	8	390	36°	950	3000K	90	25,000	35W Halogen
72547	LED8PAR16/GU10/DIM/930/FL36P [RP]	O/T	8	390	36°	950	3000K	90	25,000	35W Halogen
72676	LED8PAR16/DIM/GU10/830/FL35	N/A	8	490	35°	1300	3000K	81	25,000	60W Halogen
78896*	LED10PAR16/GU10/DIM/830/FL35	O/T	10	500	35°	1290	3000K	80	25,000	60W Halogen
72677	LED8PAR16/DIM/830/FL35	N/A	8	490	35°	1300	3000K	81	25,000	60W Halogen
78895*	LED10PAR16/DIM/830/FL35	N/A	10	500	35°	1290	3000K	80	25,000	60W Halogen



MR16										
78423	LED6MR16/DIM/827/NFL25	Yes	6	350	25°	1100	2700K	83	25,000	20W Halogen
78651*	LED6MR16/DIM/827/NFL25	N/A	6	240	25°	790	2700K	85	35,000	20W Halogen
78424	LED6MR16/DIM/827/FL36	Yes	6	350	36°	700	2700K	83	25,000	20W Halogen
78652*	LED6MR16/DIM/827/FL36	Yes	6	240	36°	440	2700K	86	35,000	20W Halogen
78421	LED6MR16/DIM/830/NFL25	Yes	6	350	25°	1300	3000K	85	25,000	20W Halogen
78634*	LED6MR16/DIM/830/NFL25	Yes	6	300	25°	860	3000K	87	35,000	20W Halogen
78422	LED6MR16/DIM/830/FL36	Yes	6	350	36°	730	3000K	85	25,000	20W Halogen
78635*	LED6MR16/DIM/830/FL36	Yes	6	300	36°	590	3000K	87	35,000	20W Halogen
78210	LED7MR16/DIM/825/NFL25	N/A	7	500	25°	1850	2500K	80	25,000	50W Halogen
78420	LED7MR16/DIM/830/NFL25	Yes	7	525	25°	2340	3000K	82	25,000	50W Halogen
78201*	LED8MR16/DIM/830/NFL25	Yes	8	525	25°	2325	3000K	82	25,000	50W Halogen
72544	LED7MR16/DIM/930/FL36P	N/A	7	400	36°	970	3000K	95	25,000	50W Halogen



*Products being phased out

N/A = Information not available at this time

O/T = Product is currently on test