


## Pan-Ty® Cable Ties – Weather Resistant Polypropylene

- For chemical resistance where high loop tensile strength is not required especially in the presence of hydrochloric acid, salts, and bases
- Greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Material requires lowering the tool setting (see table below)
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



Part Number	Length		Width		Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Tool Setting	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N				
<b>Miniature Cross Section</b>														
<b>PLT1M-M100</b>	3.9	99	.098	2.5	.043	1.1	.87	22	11	49	GTS, GTSL, GS2B, PTS, PPTS, STS2	2	1000	50000
<b>Intermediate Cross Section</b>														
<b>PLT1.5I-M100</b>	5.6	142	.142	3.6	.045	1.1	1.38	35	18	80	GTS, GTSL, GS2B, PTS, PPTS, STS2	3	1000	25000
<b>Standard Cross Section</b>														
<b>PLT2S-M100</b>	7.4	188	.190	4.8	.052	1.3	1.88	48	30	133	GTS, GTSL, GS2B, GTH, GS4H, PTS, PPTS, STS2, STH2	5 (GTS, GS2B, PTS, PPTS) 2 (GTH, GS4H)	1000	10000
<b>PLT3S-M100</b>	11.5	292	.190	4.8	.052	1.3	3.00	76	30	133			1000	10000
<b>PLT4S-M100</b>	14.5	368	.190	4.8	.052	1.3	4.00	102	30	133			1000	5000
<b>Light-Heavy Cross Section (Straight Tip)</b>														
<b>PLT2H-TL100</b>	8.1	206	.300	7.6	.075	1.9	2.00	51	50	222	GTH, GS4H, GS4EH, PTH, STH2, ST3EH	5	250	2500
<b>PLT3H-TL100</b>	11.4	290	.300	7.6	.075	1.9	3.00	76	50	222		5	250	2500
<b>PLT4H-TL100</b>	14.5	368	.300	7.6	.075	1.9	4.00	102	50	222		5	250	2500

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index

# PANDUIT® ELECTRICAL SOLUTIONS

A. System Overview	Part Number	Page Number	Part Number	Page Number	Part Number	Page Number
B1. Cable Ties	HSTTV93-48-5	C3.34	HSTTV50-T	C3.30	HVMPM32-C0	B2.21, B1.62
	HSTTV05-48-Q	C3.28	HSTTV50-T2	C3.30	HVTM-06-C0	B2.11
	HSTTV05-48-TL	C3.28	HSTTV50-T4	C3.30	HVTM3S10-C0	B1.62
B2. Cable Accessories	HSTTV05-C	C3.29	HSTTV50-T6	C3.30	HWS2819-C	B2.43
	HSTTV05-M	C3.30	HSTTV50-Y	C3.31	<b>I</b>	
	HSTTV05-M2	C3.30	HSTTV75-48-5	C3.28	ICF10IW-X	C2.61
	HSTTV05-M4	C3.30	HSTTV75-48-CQ	C3.28	ICF3IW-E	C2.61
	HSTTV05-M6	C3.30	HSTTV75-C	C3.29	ICF5IW-E	C2.61
	HSTTV05-Q	C3.31	HSTTV75-Q	C3.31	ICFC10IW-X	C2.62
B3. Stainless Steel Ties	HSTTV05-Y	C3.31	HSTTV75-T	C3.30	ICFC3IW-X	C2.62
	HSTTV06-48-Q	C3.28	HSTTV75-T2	C3.30	ICFC5IW-X	C2.62
	HSTTV06-48-TL	C3.28	HSTTV75-T4	C3.30	ICFX10IW-X	C2.57, C2.63
	HSTTV06-C	C3.29	HSTTV75-T6	C3.30	ICFX3IW-X	C2.63
C1. Wiring Duct	HSTTV06-M	C3.30	HSTTV75-Y	C3.31	ICFX5IW-X	C2.63
	HSTTV06-M2	C3.30	HSTTV100-48-5	C3.35	ILT2S-C	B1.61
	HSTTV06-M4	C3.30	HSTTV100-Y	C3.36	ILT2S-C0	B1.61
	HSTTV06-M6	C3.30	HSTTV12-48-Q	C3.35	ILT3S-C	B1.61
	HSTTV06-Q	C3.31	HSTTV19-48-Q	C3.35	ILT3S-C0	B1.61
	HSTTV06-Y	C3.31	HSTTV19-Y	C3.36	ILT4LH-TL	B1.61
C2. Surface Raceway	HSTTV09-48-Q	C3.28	HSTTV19-Y	C3.36	ILT4LH-TL0	B1.61
	HSTTV09-48-TL	C3.28	HSTTV25-48-Q	C3.35	ILT4S-C	B1.61
	HSTTV09-C	C3.29	HSTTV25-Y	C3.36	ILT4S-C0	B1.61
	HSTTV09-M	C3.30	HSTTV38-48-Q	C3.35	ILT6LH-C	B1.61
	HSTTV09-M2	C3.30	HSTTV38-Y	C3.36	ILT6LH-C0	B1.61
	HSTTV09-M4	C3.30	HSTTV50-48-5	C3.35	IT9100-C0	B1.63
C3. Abrasion Protection	HSTTV09-M6	C3.30	HSTTV50-Y	C3.36	IT9100-CUV16B	B1.63
	HSTTV09-Q	C3.31	HSTTV75-48-5	C3.35	IT9100-CUV2	B1.63
	HSTTV09-Y	C3.31	HSTTV75-Y	C3.36	IT9100-CUV4Y	B1.63
	HSTTV100-48-5	C3.28	HT2-BLU	E5.33	IT9100-CUV6	B1.63
C4. Cable Management	HSTTV100-48-LQ	C3.28	HT2-GRN	E5.33	IT9100-CUV6A	B1.63
	HSTTV100-C	C3.29	HT2-ORN	E5.33	IT9100-CUV7A	B1.63
	HSTTV100-C5	C3.29	HT2-RED	E5.33	IT9100-CUV8	B1.63
	HSTTV100-Q	C3.31	HT2-WHT	E5.33	IT9115-C0	B1.63
	HSTTV100-T2	C3.30	HT2-YEL	E5.33	IT9115-CUV11	B1.63
	HSTTV100-Y	C3.31	HT2S-BLK-YEL	E5.33	IT9115-CUV16B	B1.63
D1. Terminals	HSTTV12-48-Q	C3.28	HT2S-RED-WHT	E5.33	IT9115-CUV18	B1.63
	HSTTV12-48-TL	C3.28	HT3S-BLK-YEL	E5.33	IT9115-CUV2	B1.63
	HSTTV12-C	C3.29	HT3S-RED-WHT	E5.33	IT9115-CUV2A	B1.63
	HSTTV12-M	C3.30	HTB3-C-M	E5.36	IT9115-CUV4A	B1.63
D2. Power Connectors	HSTTV12-M2	C3.30	HTB3-DNE-M	E5.36	IT9115-CUV4Y	B1.63
	HSTTV12-M4	C3.30	HTB3-HV-M	E5.36	IT9115-CUV5A	B1.63
	HSTTV12-M6	C3.30	HTCT2-2-1	D3.14	IT9115-CUV5B	B1.63
	HSTTV12-Q	C3.31	HTCT250-2-1	D3.14	IT9115-CUV6	B1.63
D3. Grounding Connectors	HSTTV12-Y	C3.31	HTCT250-250-1	D3.14	IT9115-CUV6A	B1.63
	HSTTV150-48-5	C3.28	HTCT6X-6X-1	D3.14	IT9115-CUV6B	B1.63
	HSTTV150-C	C3.29	HTDU2B-W	E5.35	IT9115-CUV7A	B1.63
	HSTTV19-48-Q	C3.28	HTDU20-FO	E5.35	IT9115-CUV8	B1.63
	HSTTV19-48-TL	C3.28	HTDU20-T	E5.35	IT940-C0	B1.63
	HSTTV19-C	C3.29	HTDU2R-E	E5.35	IT965-C0	B1.63
E1. Labeling Systems	HSTTV19-M	C3.30	HTDU30-FO	E5.35	<b>J</b>	
	HSTTV19-M2	C3.30	HTDU30-T	E5.35	J214-312-T	D1.68
	HSTTV19-M4	C3.30	HTDU3R-E	E5.35	J216-410-L	D1.68
	HSTTV19-M6	C3.30	HTDU60-FO	E5.35	J318-412-T	D1.68
E2. Labels	HSTTV19-Q	C3.31	HTDU6R-E	E5.35	JB1DIW-A	C2.39
	HSTTV19-Y	C3.31	HTMT	B3.15	JB1FSIW-A	C2.34, C2.39
	HSTTV25-48-Q	C3.28	HTU3G-T-M	E5.35	JB1IW-A	C2.39
	HSTTV25-48-TL	C3.28	HTU30-FO-M	E5.35	JBA-X	C2.39
	HSTTV25-C	C3.29	HTU30-T-M	E5.35	JBD1	C2.41
	HSTTV25-D	C3.30	HTU3R-E-M	E5.35	JBD2	C2.41
E3. Pre-Printed & Write-On Markers	HSTTV25-D2	C3.30	HTU3Y-E-M	E5.35	JBP1DIW	C2.40
	HSTTV25-D4	C3.30	HTU60-FO	E5.35	JBP1EIW	C2.40
	HSTTV25-D6	C3.30	HTU60-TV	E5.35	JBP1FSIW	C2.34, C2.41
	HSTTV25-Q	C3.31	HTU6R-E	E5.35	JBP1IIW	C2.40
E4. Permanent Identification	HSTTV25-Y	C3.31	HTU6Y-E	E5.35	JBP1IWI	C2.40
	HSTTV38-48-Q	C3.28	HTU6Y-G	E5.35	JBP1MD20IW	C2.41, C2.43
	HSTTV38-48-TL	C3.28	HTWC2-2-1	D3.15	JBP1MR20IW	C2.41, C2.43
	HSTTV38-C	C3.29	HTWC250-2-1	D3.15	JBP2DIW	C2.39, C2.40
	HSTTV38-Q	C3.31	HTWC250-250-1	D3.15	JBP2FSIW	C2.34, C2.41
	HSTTV38-T	C3.30	HTWC6X-6X-1	D3.15	JBP2IW	C2.39, C2.40
E5. Lockout/Tagout & Safety Solutions	HSTTV38-T2	C3.30	HV9100-C	B1.64	JBP2SIW	C2.41
	HSTTV38-T2	C3.30	HV9100-C0	B1.62	JBX3510IW-A	C2.39
	HSTTV38-T4	C3.30	HV9150-C0	B1.62	JMCB-X	C4.8
	HSTTV38-T6	C3.30	HV9250-C0	B1.62	JMCMB25-1-X	C4.8
	HSTTV38-Y	C3.31	HV965-C0	B1.62		
	HSTTV50-48-Q	C3.28				
F. Index	HSTTV50-48-T	C3.28				
	HSTTV50-C	C3.29				
	HSTTV50-Q	C3.31				