



Mercury Vapor Standard

Mercury Vapor 75W Med BD17 CO

Mercury Vapor lamps feature low initial cost, but have higher operating costs than HPS or Metal Halide due to its lower efficiency. The clear mercury bulb has a bluish green appearance and the Deluxe White has a higher color rendering. Mercury lamps get dimmer over time and rarely burn out, so it is wise to replace them and restore light level.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Bulb	ED55 [ED 55mm]
Bulb Material	Hard Glass
Bulb Finish	Coated
Operating Position	Universal [Any or Universal (U)]
Life to 5% failures	6000 hr
Life to 20% failures	12000 hr
RatedAvgLife(See Family Notes)	20000 hr

• Light Technical Characteristics

Color Code	542 [CCT of 4200K]
Color Rendering Index	45 Ra8
Color Designation	Cool White
Color Temperature	4000 K
Chromaticity Coordinate X	375 -
Chromaticity Coordinate Y	370 -
Initial Lumens	3300 Lm
Luminous Efficacy	44 Lm/W
Lamp EM	
Lumen Maintenance 2000h	92 %
Lumen Maintenance 5000h	90 %

• Electrical Characteristics

Watts	75 W
-------	------

Lamp Wattage	75 (nom), 80 (max) W
Lamp Voltage	130 V
Lamp Current EM	0.66 A
Dimmable	No

• Environmental Characteristics

Mercury (Hg) Content	17.8 mg
----------------------	---------

• Luminaire Design Requirements

Cap-Base Temperature	200 (max) C
Bulb Temperature	350 (max) C

• Product Dimensions

Overall Length C	138 (max) mm
Diameter D	56 (max) mm

• Product Data

Product number	275248
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677275242
Bar code on case	50046677275247
Logistics code(s)	928486000091
eop_net_weight_pp	0.060 kg

PHILIPS

sense and simplicity


Mercury Vapor Standard

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or

other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing




HPL, E26/E27/E39/E40

Product	C (Max)	D (Max)
HPL N 75W E26 HG	138	56



E26

Photometric data





© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change