

LED 12-20

Fluorescent 21-51

Compact Fluorescent 52-69

High Intensity Discharge 70-99

SPECIALTY LAMPS

ANSI Code	Product Number	Pkg. Qty.	Volts	Avg. Watts (Amps)	Bulb	Base	Rated Avg. Life (Hrs.) ^a	Coil Type	LCL (In.)	LCL (mm.)	MOL (In.)	MOL (mm.)	Rated Approx. Lumens	Color Temp (K)	Operating Position
PHOTO PROJECTION LAMPS															
BRL	31627-3	24	12	50	T3.5	G6.35	50	C-6	1 1/8	30	1 7/8	44	1500	3400	BDTH
DDL	31509-3	24	20	150	MIR 16	GX5.3	500	CC-6	—	—	1 1/2	44.5	—	3150	BDTH
DZA	28117-0	100	10.8	30	T5	G5.3	1000	—	—	—	1 1/8	47	570	3100	BDTH
EFN	31502-8	50	12	75	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3350	BDTH
EFP	31488-0	50	12	100	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3350	BDTH
EFP/8H	13657-2	50	12	100	MIR 16	GZ6.35	800	C-6	—	—	1 1/8	42	—	3100	BDTH
EFR	31490-6	50	15	150	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3350	BDTH
BHJ	31758-6	100	24	250	T4	G6.35	50	C-6F	1 1/8	33	2 1/8	55	9400	3400	BD
BHJ-SH	14169-7	100	24	250	T4	G6.35	500	C-6F	1 1/8	33	2 1/8	55	9400	3200	BD
BHJ-X	23175-3	200	24	250	T4	G6.35	50	C-6F	1 1/8	33	2 1/8	55	10,000	3400	BD
EJA	44142-8	24	21	150	MIR 16	GX5.3	40	CC-6	—	—	1 1/8	44.5	—	3350	BDTH
EJL	31508-5	24	24	200	MIR 16	GX5.3	50	CC-6	—	—	1 1/8	44.5	—	3400	BDTH
EJM	23942-6	24	21	150	MIR 16	GX5.3	40	CC-6	—	—	1 1/8	44.5	—	3400	BDTH
BKE	31592-9	24	21	150	MIR 16	GX5.3	200	CC-6	—	—	1 1/8	44.5	—	3400	BDTH
ELC	23103-5	24	24	250	MIR 16	GX5.3	50	CC-6	—	—	1 1/8	44.5	—	3200	BDTH
ELC-S	38166-5	24	24	250	MIR 16	GX5.3	500	CC-6	—	—	1 1/8	44.5	—	3200	BDTH
ELD	31618-2	24	21	150	MIR 16	GX5.3	40	CC-6	—	—	1 1/8	44.5	—	3350	BDTH
ELH	31619-0	24	120	300	MIR 16	GY5.3	35	CC-8	—	—	1 1/8	44.5	—	3350	BDTH
BNH	31621-6	24	120	250	MIR 16	GX5.3	175	CC-8	—	—	1 1/8	44.5	—	3250	BDTH
BNX	31927-7	24	82	360	MIR 16	GY5.3	75	CC-8	—	—	1 1/8	44.5	—	3300	BDTH
ESV/BHD	26126-3	100	6	10	T2.5	G4	100	C-6	3/8	19.6	1 1/8	30	200	3200	ANY
ESB	25678-4	100	6	20	T3	G4	100	C-6	3/8	19.5	1 1/8	31	420	3200	ANY
EVA	25676-8	100	12	100	T3.5	GY6.35	1000	C-6F	1 1/8	30	1 7/8	44	2500	3200	ANY
EVC	31884-0	24	24	250	T5	G6.35	300	C-6F	1 1/8	33	2 1/8	57	8400	3200	ANY
EVC 10H	20982-5	100	24	250	T5	G6.35	1000	C-6F	1 1/8	33	2 1/8	57	8400	3200	ANY
EVD-X	23177-9	24	36	400	T6	G6.35	50	C-6F	1 1/8	36.1	2 1/8	59.9	16,625	3400	BDTH
EXR	25286-6	24	82	300	MIR 13	GX5.3	35	CC-8	—	—	1 1/8	44.45	—	3350	BDTH
EYB	23257-9	24	82	360	T5	G5.3	75	CC-8	1 1/8	31	2 1/8	57	10,000	3250	BDTH
FCM	33269-2	12	120	1000	T3	R7s	300	C-8	—	—	4 1/8	119.9	27,000	3200	HORIZ.
FCR	26101-6	100	12	100	T3.5	GY6.35	50	C-6F	1 1/8	30	1 7/8	44	3400	3400	BDTH
FCS	20607-8	200	24	150	T4	G6.35	50	C-6F	1 1/8	30	2	50.8	5200	3400	BDTH
FCS-X	23174-6	100	24	150	T4	G6.35	50	C-6F	1 1/8	30	2	50.8	6000	3400	BDTH
FHS	25305-4	24	82	300	MIR 13	GX5.3	70	CC-8	—	—	1 1/8	44.45	—	3300	BDTH
FJX	31499-7	50	13.8	30	MIR 16	GX5.3	500	C-8	—	—	1 1/8	44.9	—	3150	ANY
RLW	20492-5	24	24	300	T6	GY6.3	50	C-6F	1 1/8	33	2 1/8	55	10,450	3400	BD±15°
GDA	38684-7	100	120	500	T3.5	R7s	75	CC-8	—	—	5 1/8	133.3	11,000	3200	ANY
JCR 15v 150W	24923-5	24	15	150	MIR 16	GZ6.35	500	C-8	—	—	1 1/8	42	—	—	BDTH
5761	25713-9	100	6	30	T3.5	G4	100	C-6F	3/8	19.6	1 1/8	31	765	3200	ANY
6605	25684-2	100	6	10	T3	G4	2000	C-6	3/8	19.5	1 1/8	30	150	2700	ANY
6982P	13421-3	10	230	800	T6	G 9.5	300	BiPlane	2 1/8	60.5	4 1/8	104	20,000	3200	ANY
7010	14664-7	20	120	300	T6	GX6.35	150	C-6	1 1/8	32.5	—	—	7500	3200	ANY
13117	37614-5	50	17	150	MIR 16	GX5.3	1000	CC-6	—	—	1 1/8	47	—	3200	ANY
13139	33545-5	50	12	75	MIR 16	GZ6.35	25	C-8	—	—	1 1/8	42	—	3400	BD±105°
13165	44295-4	50	14	35	MIR 11	GZ4	50	—	—	—	1 1/8	38	—	—	BD±130°
13298	16094-5	50	10	52	MIR 11	GZ4	20	CC-8	—	—	1 1/8	44.9	—	—	HORIZ±40°
13477R	31349-4	150	220	800	T3.5	R7s	150	—	—	—	4 1/8	120	21,600	3200	HORIZ.
13528	31504-4	360	6	15	MIR 11	GZ4	500	C-6	—	—	1 1/8	38	—	—	BD±105°
13865	26423-4	50	12	75	MIR 11	G5.3	50	—	—	—	1 1/8	40	—	—	BD±105°
14553	26391-3	230	10	52	MIR 11	GZ4	20	—	—	—	1 1/8	40	—	—	BD±105°
14623	15881-6	100	17	95	T4	GY6.35	2000	C-8	—	—	1 1/8	50	2150	3000	ANY

^aRated average life is the length of operation (in hours) at which point 50% of a large sample of lamps will still be operational and 50% will not.

For the most current product information go to the e-catalog on www.philips.com

