

# SPECIALTY LAMPS

Product Number	Ordering Code	Watts	Description	Nom. Length (In.)	Bulb	Base	Rated Avg. Life (Hrs.)*	UVA Watts
<b>15752-9</b>	PL-S 9W/08 (Lead Free)	9	UVA Lamp	6½	PL-S	G23	3000	
<b>15766-9</b>	PL-S 9W/10 (Lead Free)	9	UVA Lamp	6½	PL-S	G23	2000	1.9
<b>15765-1</b>	PL-S 9W/10/2P (Lead Free)	9	UVA Lamp	6½	PL-S	G23	9000	
<b>13036-9</b>	F15T8/BL	15	Black Light	18	T8	Med. Bipin	5000	3.1
<b>13034-4</b>	PL-L 18W/10	18	UVA Lamp	9	PL-L	2GI I	5000	3.4
<b>23293-4</b>	PL-L 36W/10/4P	36		15½	PL-L	2GI I	2000	
<b>39153-2</b>	Actinic BL 40W/10	40	Black Light	48	T12	Med. Bipin	9000	9
<b>24675-1</b>	TLK 40W/10R	40	UVA Reflector Lamp	24	T12	Med. Bipin	3000	7.4
<b>26169-3</b>	TL 60W/10R	60	UVA Reflector Lamp	48	T12	Med. Bipin	1000	15.8
<b>26885-4</b>	TL 80W/10R	80	UVA Reflector Lamp	60	T12	Med. Bipin	1000	20.5
<b>24694-2</b>	TL 100W/10R	100	UVA Reflector Lamp	70	T12	Med. Bipin	1000	26.6
<b>21513-7</b>	Actinic BL 8W/10	8	UVA Lamp	20	T5	Min. Bipin	3000	
<b>21517-8</b>	Actinic BL 30W/10	30	UVA Lamp	24	T8	Med. Bipin	2000	
<b>21514-5</b>	Actinic BL TL-K 40W/10	40	UVA Lamp	24	T12	Med. Bipin	2000	

\* Rated average Life is the length of operation (in hours) at which point 50% of a large sample of lamps will still be operational and 50% will not

1) For graphic arts, lacquer curing and insect trap applications

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)



PL-S UVA Lamp      F15T8/BL      PL-L UVA Lamp      T12 Black Light Med. Base      TLK UVA Reflector Lamp      TL UVA Lamp      TL UVA Reflector Lamp      T8 Actinic UVA Lamp Med. Bipin      T12 Actinic UVA Lamp Med. Bipin