

Mercury Vapor Standard

Mercury Vapor 250W Mog ED28 CO



Mercury Vapor lamps feature low initial cost, but have higher operating costs than HPS or Metal Halide due to its lower efficiency. The clear mercury bulb has a bluish green appearance and the Deluxe White has a higher color rendering. Mercury lamps get dimmer over time and rarely burn out, so it is wise to replace them and restore light level.

Product data

• General Characteristics

Base	Mogul [Mogul]
Bulb	ED-28 [ED 90mm]
Bulb Material	Hard Glass
Bulb Finish	Coated
Operating Position	Universal [Any or Universal (U)]
Life to 5% failures	5000 hr
Life to 20% failures	10000 hr
RatedAvgLife(See Family Notes)	15000 hr

• Light Technical Characteristics

Color Code	542 [CCT of 4200K]
Color Rendering Index	40 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Chromaticity Coordinate X	381 -
Chromaticity Coordinate Y	383 -
Initial Lumens	12000 Lm
Luminous Efficacy Lamp EM	48 Lm/W
Lumen Maintenance 2000h	88 %
Lumen Maintenance 5000h	85 %

• Electrical Characteristics

Watts	250 W
-------	-------

Lamp Wattage	250 (nom), 263 (max) W
Lamp Voltage	135 V
Lamp Current EM	2.1 A
Dimmable	No

• Environmental Characteristics

Mercury (Hg) Content	38 mg
----------------------	-------

• Luminaire Design Requirements

Cap-Base Temperature	210 (max) C
Bulb Temperature	350 (max) C

• Product Dimensions

Overall Length C	211 (max) mm
Diameter D	91 (max) mm

• Product Data

Product number	248146
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677248147
Bar code on case	50046677248142
Logistics code(s)	928485100091
eop_net_weight_pp	0.165 kg


Mercury Vapor Standard

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or


other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing




HPL, E26/E27/E39/E40

Product	C (Max)	D (Max)
HPL N 250W E39 HG	211	91



E39

Photometric data





© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change