

Incandescent 20-51

Halogen 52-70

Compact Fluorescent 71-86

Fluorescent 87-120

SPECIALTY LAMPS

ANSI Code	Product Number	Pkg. Qty.	Volts	Avg. Watts (Amps)	Bulb	Base	Rated Avg. Life (Hrs.) ^a	Coil Type	LCL (In.)	LCL (mm.)	MOL (In.)	MOL (mm.)	Rated Approx. Lumens	Color Temp (K)	Operating Position
PHOTO PROJECTION LAMPS															
BRL	31627-3	24	12	50	T3.5	G6.35	50	C-6	1 1/8	30	1 7/16	44	1500	3400	BDTH
BVE	23922-8	24	120	625	T6	G9.5	75	C-13D	1 1/2	44.5	3 1/2	89	—	3350	BDTH
DDL	31509-3	24	20	150	MIR 16	GX5.3	500	CC-6	—	—	1 1/2	44.5	—	3150	BDTH
DDM	23937-6	24	19	80	MIR 16	GX5.3	50	CC-6	—	—	1 1/2	44.5	—	3350	BDTH
DDS	31510-1	24	21	80	MIR 16	GX5.3	1000	CC-6	—	—	1 1/2	44.5	—	3125	BDTH
DNF	25241-1	24	21	150	MIR 16	GX7.9	25	CC-6	—	—	1 1/8	45.24	—	3400	HORIZ.
DYS/DYV	31639-8	24	120	600	G7	GZ9.5	75	CC-6	1 1/2	36.5	2 1/2	63.5	17,000	3200	HORIZ.
DZA	28117-0	100	10.8	30	T5	G5.3	1000	—	—	—	1 1/8	47	570	3100	BDTH
EFM	31484-9	50	8	50	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3300	BDTH
EFN	31502-8	50	12	75	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3350	BDTH
EFP	31488-0	50	12	100	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3350	BDTH
EPF/BH	13657-2	50	12	100	MIR 16	GZ6.35	800	C-6	—	—	1 1/8	42	—	3100	BDTH
EFR	31490-6	50	15	150	MIR 16	GZ6.35	50	C-6	—	—	1 1/8	42	—	3350	BDTH
BHA	31641-4	24	120	500	T6	GZ9.5	50	C-13D	1 1/2	36.5	3	76.2	11,000	3250	BDTH
BHJ	31758-6	100	24	250	T4	G6.35	50	C-6F	1 1/8	33	2 1/8	55	9400	3400	BD
BHJ-SH	14169-7	100	24	250	T4	G6.35	500	C-6F	1 1/8	33	2 1/8	55	9400	3200	BD
BHJ-X	23175-3	200	24	250	T4	G6.35	50	C-6F	1 1/8	33	2 1/8	55	10,000	3400	BD
BA	44142-8	24	21	150	MIR 16	GX5.3	40	CC-6	—	—	1 1/8	44.5	—	3350	BDTH
BJL	31508-5	24	24	200	MIR 16	GX5.3	50	CC-6	—	—	1 1/8	44.5	—	3400	BDTH
BJM	23942-6	24	21	150	MIR 16	GX5.3	40	CC-6	—	—	1 1/2	44.5	—	3400	BDTH
BJV	33744-4	24	21	150	MIR 16	GX5.3	40	CC-8	—	—	1 1/2	44.5	—	3400	BDTH
BKE	31592-9	24	21	150	MIR 16	GX5.3	200	CC-6	—	—	1 1/2	44.5	—	3400	BDTH
BKE LL	14133-3	24	21	150	MIR 16	GX5.3	1000	CC-6	—	—	1 1/2	44.5	—	3400	BDTH
BKZ	23945-9	24	10.8	30	MIR 16	GX5.3	200	CC-6	—	—	1 1/2	44.5	—	3100	BDTH
ELC	23103-5	24	24	250	MIR 16	GX5.3	50	CC-6	—	—	1 1/2	44.5	—	3200	BDTH
ELC-S	38166-5	24	24	250	MIR 16	GX5.3	500	CC-6	—	—	1 1/2	44.5	—	3200	BDTH
ELD	31618-2	24	21	150	MIR 16	GX5.3	40	CC-6	—	—	1 1/8	44.5	—	3350	BDTH
ELH	31619-0	24	120	300	MIR 16	G5.3	35	CC-8	—	—	1 1/8	44.5	—	3350	BDTH
ENG	23951-7	24	120	300	MIR 16	G5.3	15	CC-8	—	—	1 1/2	44.5	—	3450	BDTH
BNH	31621-6	24	120	250	MIR 16	G5.3	175	CC-8	—	—	1 1/2	44.5	—	3250	BDTH
BNX	31927-7	24	82	360	MIR 16	G5.3	75	CC-8	—	—	1 1/2	44.5	—	3300	BDTH
BNX-S	20497-4	24	86	360	MIR 16	G5.3	75	CC-8	—	—	1 1/2	44.5	—	3300	BDTH
ESA/BHD	26126-3	100	6	10	T2.5	G4	100	C-6	3/8	19.6	1 1/8	30	200	3200	ANY
ESB	25678-4	100	6	20	T3	G4	100	C-6	3/8	19.5	1 1/8	31	420	3200	ANY
EVA	25676-8	100	12	100	T3.5	G6.35	1000	C-6F	1 1/8	30	1 7/16	44	2500	3200	ANY
EVC	31884-0	24	24	250	T5	G6.35	300	C-6F	1 1/8	33	2 1/8	57	8400	3200	ANY
EVC 10H	20982-5	100	24	250	T5	G6.35	1000	C-6F	1 1/8	33	2 1/8	57	8400	3200	ANY
EVD-X	23177-9	24	36	400	T6	G6.35	50	C-6F	1 1/8	36.1	2 1/8	59.9	16,625	3400	BDTH
EVW	25284-1	24	82	250	MIR 16	GX5.3	50	CC-8	—	—	1 1/2	44.5	—	3300	BD ± 22°
EGR	25286-6	24	82	300	MIR 13	GX5.3	35	CC-8	—	—	1 1/2	44.5	—	3350	BDTH
EXW	23971-5	24	82	300	MIR 13	GX5.3	15	CC-8	—	—	1 1/2	44.5	—	3400	BDTH
EXY	20493-3	24	82	250	MIR 13	GX5.3	250	CC-8	—	—	1 1/2	44.5	—	3250	BDTH
EYB	23257-9	24	82	360	T5	G5.3	75	CC-8	1 1/2	31	2 1/2	57	10,000	3250	BDTH
FCM	33269-2	12	120	1000	T3	R7s	300	C-8	—	—	4 1/8	119.9	27,000	3200	HORIZ.
FCR	26101-6	100	12	100	T3.5	G6.35	50	C-6F	1 1/8	30	1 7/16	44	3400	3400	BDTH
FCS	20607-8	200	24	150	T4	G6.35	50	C-6F	1 1/8	30	2	50.8	6000	3400	BDTH
FCS-X	23174-6	100	24	150	T4	G6.35	50	C-6F	1 1/8	30	2	50.8	6000	3400	BDTH
RDS/DZE	31655-4	24	24	150	T4.5	GZ9.5	50	C-6F	1 1/8	33.4	2 1/2	57	5000	3400	BD

† — New products

^a Rated average life is the length of operation (in hours) at which point 50% of a large sample of lamps will still be operational and 50% will not. For the most current product information go to the e-catalog on www.philips.com



160 Philips Lighting Company SAG100 2008-2009