

MasterColor CDM-T T6

MasterColor CDM-T 35W/830 T6 1CT



MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Product data

• General Characteristics

Base	G12
Bulb	T6 [Diameter: 6/8 inch /19mm]
Bulb Finish	Clear
Operating Position	Universal [Any or Universal (U)]
Avg. Life	12000 hr
Avg. Hrs. Life	12000 hr
Life to 10% failures EM	9000 hr
Life to 5% failures EL	8000 hr
Life to 5% failures EM	8000 hr
Life to 20% failures EL	10000 hr
Life to 20% failures EM	10000 hr
Life to 10% failures EL	9000 hr

• Light Technical Characteristics

Color Code	830 [CCT of 3000K]
Color Rendering Index	81 Ra8
Color Designation	Warm White
Color Temperature	3000 K
Color Temperature technical	3095 K
Chromaticity Coordinate X	0.428 -
Chromaticity Coordinate Y	0.397 -
Initial Lumens	3150 Lm
Initial Lumens	3150 Lm
Luminous Efficacy Lamp EM	87 Lm/W
Luminous Efficacy Lamp EL	83 Lm/W

Lumen Maintenance EM 2000h	75 %
Lumen Maintenance EL 2000h	80 %
Lumen Maintenance EM 5000h	65 %
Lumen Maintenance EL 5000h	70 %
Lumen Maintenance EM 10000h	45 %
Lumen Maintenance EL 10000h	50 %
Design Mean Lumens EL	2250 Lm
Design Mean Lumens EM	2000 Lm

• Electrical Characteristics

System Power EM	47 W
System Power EL	44 W
Watts	35 W
Lamp Wattage	38.0 W
Lamp Wattage EL	38 W
Lamp Voltage	88 V
Lamp Current EM	0.53 A
Lamp Current EL	0.47 A
Ignition Time	30 (max) s
Run-up time 90%	3 (max) min
Ignition Peak Voltage	3500 (min) V
Re-ignition Time [min]	15 (max) min
Dimmable	No

PHILIPS

sense and simplicity

• Environmental Characteristics

Mercury (Hg) Content 3.1 mg

• UV-related Characteristics

PET (NIOSH) 44 h.klx
Damage Factor D/fc 0.27 -

• Luminaire Design Requirements

Cap-Base Temperature 280 (max) C
Pinch Temperature 350 (max) C
Bulb Temperature 500 (max) C

• Product Dimensions

Reference Length A 90 (max) mm
Overall Length C 103 (max) mm
Diameter D 20 (max) mm
Light Center Length L 55 (min), 56 (nom), 57 (max) mm

Arc Length O 5 mm
Light Center Length L 2.21875 in
Max Overall Length (MOL) - C 3.9375 (max) in
Diameter D 0.75 in

• Product Data


Product number 223289
Full product name MASTERColour CDM-T
Short product name MASTERColour CDM-T
Pieces per Sku 1
eop_pck_cfg 12
Skus/Case 12
Bar code on pack 46677223281
Bar code on case 50046677223286
Logistics code(s) 928083105117
tpd_ilcos_cd MT-35/30/1B-H-G12
eop_net_weight_pp 0.027 kg

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will

remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing



CDM-T


Product	C (Max)	D (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
CDM-T 35W/830 G12	103	20	55	56	57	5

Dimensional drawing



G12

Photometric data



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change