



# Reflector Flood

Reflector 300W Mog 120V R40 FL FR 1CT

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

## Product data

### • General Characteristics

Base	Mogul [Mogul]
Base Information	Brass [Brass Base]
Bulb	R40
Bulb Finish	Frosted
Filament Shape	CC11 [V-shape above glass button (cylindriform)]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
Circle E logo	Yes

### • Light Technical Characteristics

Beam Description	Flood [Flood]
Initial lumen	3600 Lm

### • Electrical Characteristics

Watts	300 W
Voltage	120 V

### • Product Dimensions

Max Overall Length (MOL) - C	7.25 (max) in
------------------------------	---------------

Diameter D 5 in

### • Footnotes


Footnotes Incandescent	920 [Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.]
------------------------	--

### • Product Data

Product number	144337
Full product name	Reflector 300W Mog 120V R40 FL FR 1CT
Short product name	Refl 300W Mog 120V R40 FL FR 1CT
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677144333
Bar code on case	50046677144338
Logistics code(s)	920673635501
eop_net_weight_pp	0.001 kg


## Dimensional drawing

## Dimensional drawing



### E26/E39, R40

Product	C (Max)	D (Norm)
300W E39 120V R40 FL	7.25	5



E39



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, July 31  
data subject to change