



MasterColor® CDM PAR30L

MasterColor CDM 70W/830 Med PAR30L SP 1CT

Philips MasterColor® Ceramic Metal Halide PAR30L Lamps offer high-efficiency, ceramic metal halide reflector lamps with a stable color over lifetime and a crisp, sparkling light.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Nic/Brass [Nickel/Brass Base]
Bulb	PAR30L [PAR 3.75 inch/95mm Long]
Bulb Material	Hard Glass
Bulb Finish	Reflector
Operating Position	Universal [Any or Universal (U)]
Main Application	General Lighting
RatedAvgLife(See Family Notes)	11000 hr

• Light Technical Characteristics

Beam Description	Spot
Beam Angle	10 D
Approx. MBCP	68000 cd
Color Code	830 [CCT of 3000K]
Color Rendering Index	78 (min), 82 (nom) Ra8
Color Temperature	3000 K
Color Temperature technical	3000 K
Chromaticity Coordinate X	432 -
Chromaticity Coordinate Y	390 -
Initial Lumens	5000 Lm
Luminous Efficacy Lamp	71.4 Lm/W
Lumen Maintenance 5000h	65 %
Design Mean Lumens	3050 Lm

• Electrical Characteristics

Watts	70 W
-------	------

Lamp Wattage Technical	79 W
Lamp Voltage	102 V
Lamp Current	0.93 A
Ignition Time	30 (max) s
Re-ignition Time [min]	10 (max) min

• Environmental Characteristics

Mercury (Hg) Content	10.1 (max) mg
----------------------	---------------

• UV-related Characteristics

PET (NIOSH)	100 h.klx
Damage Factor D/fc	0.25 -

• Luminaire Design Requirements

Cap-Base Temperature	200 (max) C
Bulb Temperature	300 (max) C

• Product Dimensions

Max Overall Length (MOL) - C	4.750 (max) in
Diameter D	3.740 in

• Product Data

Product number	232249
Full product name	MasterColor CDM 70W/830 Med PAR30L SP 1CT
Short product name	CDM 70W/830 Med PAR30L SP 1CT
Pieces per Sku	1

PHILIPS

sense and simplicity

eop_pck_cfg 6
 Skus/Case 6
 Bar code on pack 46677232245

Bar code on case 50046677232240
 Logistics code(s) 928601133301
 eop_net_weight_pp 0.001 kg

Warnings and Safety


- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will

remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

Dimensional drawing

E26, PAR30L

Product	C (Max)	D (Norm)
CDM 70W/830 E26 PAR30L SP 10D U FB	4.750	3.740



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change