

# EcoVantage

## EcoVantage 39W 120V FL 25D



The new EcoVantage bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

### Product data

#### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	PAR30L [PAR 3.75 inch/95mm Long]
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Track, Downlighting & Outdoor
Atmosphere	Gas
RatedAvgLife(See Family Notes)	1100 hr

#### • Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	25 D
Approx. MBCP	2350 cd
Color Rendering Index	100 Ra8
Color Temperature	2900 K
Initial lumen	520 Lm

#### • Electrical Characteristics

Watts	39 W
Voltage	120 V

#### • Product Dimensions

Max Overall Length (MOL) - C	4.5 (max) in
Diameter D	3.75 in


#### • Product Data

Product number	428870
Full product name	EcoVantage 39W 120V FL 25D
Short product name	39PAR30L/EVP/FL25 120V 15/1
Pieces per Sku	1
Skus/Case	15
Bar code on pack	46677428877
Bar code on case	50046677428872
Logistics code(s)	925707136303
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

Dimensional drawing



EcoVantage 39W 120V FL 25D



EcoVantage 39W 120V FL 25D



E26



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, December 1  
data subject to change