

Energy Advantage IR PAR38



Energy Advantage IR 40W Med Skt 120V PAR38 DiOptic
SP 10D CL

Philips Halogen Energy Advantage IR PAR Lamps combine visual appeal with energy savings and long life. These lamps provide high quality light that bring out textures in clothes and linens.

Product data

• General Characteristics

Base	Medium Skirted [Skirted Medium Screw (PAR Lamps)]
Base Information	Brass [Brass Base]
Bulb	PAR38 DiOptic
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Outdoor
Atmosphere	Gas
RatedAvgLife(See Family Notes)	4200 hr
Estimated Energy Cost/YR	4.82 \$
Life with 3h/day use [years]	3.8 an

• Light Technical Characteristics

Beam Description	Spot
Beam Angle	10 D
Approx. MBCP	11000 cd
Color Rendering Index	100 Ra8
Color Temperature	2720 K

Initial lumen 705 Lm

• Electrical Characteristics

Watts	40 W
Voltage	120 V

• Product Dimensions


Max Overall Length (MOL) - C	5.313 (max) in
Diameter D	4.75 in

• Product Data

Product number	145029
Full product name	Energy Advantage IR 40W Med Skt 120V PAR38 DiOptic SP 10D CL
Short product name	40W Med Skt 120V PAR38 DiOptic SP 10D CL
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677145026
Bar code on case	50046677145021
Logistics code(s)	924757130001
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing



E26, PAR38

Product	C (Max)	D (Norm)
PAR38 IRC 40W E26/50x39/BRC 120V SP 10D	5.313	4.75



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 11
data subject to change