



Ceramalux ALTO

Ceramalux 200W Mog ED18 CL ALTO

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

• General Characteristics

Base	Mogul [Mogul]
Base Information	Brass [Brass Base]
Bulb	ED18
Bulb Material	Hard Glass
Bulb Finish	Clear
Operating Position	Universal [Any or Universal (U)]
Main Application	General and Street Lighting
Rated Avg. Life	24000 hr

• Light Technical Characteristics

Color Rendering Index	21 Ra8
Color Temperature	2100 K
Color Temperature technical	2050 K
Chromaticity Coordinate X	521 -
Chromaticity Coordinate Y	420 -
Initial Lumens	23000 Lm
Luminous Efficacy Lamp	115 Lm/W
Design Mean Lumens	19260 Lm

• Electrical Characteristics

Watts	200 W
Lamp Voltage	100 V
Lamp Current	2.4 A
Ignition Time	5 (max) s
Re-ignition Time [min]	1 (max) min

• Environmental Characteristics

Mercury (Hg) Content	31 (max) mg
----------------------	-------------

• UV-related Characteristics

• Luminaire Design Requirements

Cap-Base Temperature	210 (max) C
Bulb Temperature	400 (max) C

• Product Dimensions

Light Center Length L	5.75 in
Max Overall Length (MOL) - C	9.75 (max) in
Diameter D	2.25 in


• Product Data

Product number	368779
Full product name	Ceramalux 200W Mog ED18 CL ALTO
Short product name	Ceramalx 200W Mog ED18 CL ALTO
Pieces per Sku	1
eop_pck_cfg	12
Skus/Case	12
Bar code on pack	46677368777
Bar code on case	50046677368772
Logistics code(s)	928601139501
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



E39, ED-18



E39, ED-18



E39



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change