

EcoVantage

EcoVantage 53W 120V PAR30S SP 10D

The new EcoVantage bulbs reduce energy consumption without sacrificing the qualities of a traditional bulb. They uniquely produce light more efficiently. They work with dimmer switches and are available in the familiar A-shape design. Use them in existing fixtures just as you would standard incandescents and your home will look great while you save energy.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	PAR30S [PAR 3.75 inch/95mm Short]
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
RatedAvgLife(See Family Notes)	1100 hr
Life with 3h/day use [years]	2.7 an
Estimated Energy Cost/YR	6.02 \$

• Light Technical Characteristics

Beam Description	Spot
Beam Angle	10 D
Approx. MBCP	6600 cd
Color Rendering Index	100 Ra8

Color Temperature 2790 K

• Electrical Characteristics

Watts 53 W
Voltage 120 V


• Product Dimensions

Max Overall Length (MOL) - C 3.625 (max) in
Diameter D 3.75 in


• Product Data

Product number 428888
Full product name EcoVantage 53W 120V PAR30S SP 10D
Short product name 53PAR30S/EVP/SP10 120V 15/1
Pieces per Sku 1
Skus/Case 15
Bar code on pack 46677428884
Bar code on case 50046677428889
Logistics code(s) 925709936302
eop_net_weight_pp 0.001 kg

Dimensional drawing



EcoVantage 53W 120V PAR30S SP 10D



EcoVantage 53W 120V PAR30S SP 10D



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, December 1
data subject to change