

Energy Saver Decoratives

5W EL/mCan T2



Philips Energy Saver Decorative CFLs provide energy savings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

Product data

• General Characteristics

Base	Candelabra [Candelabra Screw]
Bulb	EL/mCan T2
Rated Lifetime (hours)	8000 hr

Power Factor	0.55 -
Voltage	110-127 V
Lamp Current mA	90 mA
Line Frequency	50/60 Hz
Starting Time	0.2 s
Warm-up Time to 60% Light Outp	180 (max) s

• Light Technical Characteristics

Color Code	827 [CCT of 2700K]
Color Rendering Index	80 (min) Ra8
Color Designation	Warm White
Color Temperature	2700 K
Color Temperature technical	2700 K
Rated Luminous Flux	215 Lm
Luminous Efficacy	43 Lm/W
Lamp	
Lumen Maintenance 2000h	80 %
Lumen Maintenance 5000h	70 %
Chromaticity Coordinate X	459 -
Chromaticity Coordinate Y	412 -

• Product Dimensions

Overall Length C	103 (max) mm
Diameter D	40.5 (max) mm
Width F	39 (max) mm

• Product Data

Product number	422303
Full product name	5W EL/mCan T2
Short product name	EL/mCan T2 5W
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677422301
Bar code on case	50046677422306
Logistics code(s)	929689982701
eop_net_weight_pp	0.040 kg

• Electrical Characteristics

Watts	5 W
-------	-----

Dimensional drawing

Dimensional drawing

5W EL/mCan T2

Product	C (Max)	D (Max)	F (Max)
Candle 5W E12 110-127V EL/mCan T2	103	40,5	39

E12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, December 21
data subject to change