

Philips A-shape
Dimmable LED Lamp

Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, government buildings, and multi-unit residences

LED



Attractive, dimmable LED alternative to popular incandescents

Philips A-shape Dimmable LED Lamps are the smart LED alternative to standard incandescent A-shape lamps. The unique lamp design provides omni-directional light with excellent dimming performance.

High efficacy LED accent light

- New bulb shape to compliment fixtures and decor
- 8W A19 LED bulb is ENERGY STAR® Qualified and replaces a 40W incandescent equivalent A19 bulb*
- 11W A19 LED bulb is ENERGY STAR® Qualified and replaces a 60W incandescent equivalent A19 bulb**
- Smooth dimming to 10% of full light levels†
- 25,000 hour rated average life‡
- Emits virtually no UV/IR in the light beam
- Contains no mercury

Easy to experience

- Long life properties—lowers maintenance costs by reducing re-lamp frequency
- Will not fade colors, avoids inventory spoilage
- 3-year limited warranty***



PHILIPS

Philips A-shape Dimmable LED Lamp

Ordering, Electrical and Technical Data (Subject to change without notice)

| Product Number | Ordering Code | Norm. Watts | Volts | Lamps per SKU | Description | Bulb Type | Base | Rated Avg. Life (Hrs.) ¹ | Approx. Lumens ² | CRI | Color Temp. (Kelvin) | MOL (In.) |
|----------------|------------------------|-------------|-------|---------------|--|-----------|------|-------------------------------------|-----------------------------|-----|----------------------|-----------|
| A19 | | | | | | | | | | | | |
| 42348-3 | 8A19/END/2700 DIM 6/1 | 8 | 120 | 1 | 120V Bulb END 8-40W 2700K 470 Dim SOC | A19 | Med | 25000 | 470 | 81 | 2700 | 4 |
| 42349-1 | 11A19/END/2700 DIM 6/1 | 11 | 120 | 1 | 120V Bulb END 11-60W 2700K 830 Dim SOC | A19 | Med | 25000 | 830 | 81 | 2700 | 4 |

Shipping Data (Subject to change without notice)

| Product Number | SKU UPC (0-46677) | Outer Bar Code (5-00-46677) | Case Qty. | Case Weight (lbs.) | Case Cube (cu. ft.) | Pallet Qty. | SKUs Per Layer | Layers High | SKU Dimensions (W x D x H)(In.) | Case Dimensions (W x D x H)(In.) | Pallet Dimensions (W x D x H)(In.) |
|----------------|-------------------|-----------------------------|-----------|--------------------|---------------------|-------------|----------------|-------------|---------------------------------|----------------------------------|------------------------------------|
| A19 | | | | | | | | | | | |
| 42348-3 | 42348-3 | 42348-8 | 6 | 2.45 | 0.131 | 1224 | 204 | 6 | 2.72 x 2.72 x 4.80 | 8.40 x 5.60 x 4.80 | 47.20 x 39.40 x 34.90 |
| 42349-1 | 42349-0 | 42349-5 | 6 | 2.45 | 0.131 | 1224 | 204 | 6 | 2.72 x 2.72 x 4.80 | 8.40 x 5.60 x 4.80 | 47.20 x 39.40 x 34.90 |

- 1) Rated average life is based on engineering testing and probability analysis.
 2) Based on photometric testing consistent with IES LM-79.
 ■ This lamp is ENERGY STAR® Qualified.

- Footnotes from front:
 * When comparing a 8W LED A19 having 470 lumens to the standard 40W incandescent A19 having 500 lumens.
 ** When comparing a 11W LED A19 having 830 lumens to the standard 60W incandescent A19 having 800 lumens.
 *** For details see: http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd.
 1) Rated average life is based on engineering testing and probability analysis.
 † Dimmable when using leading edge dimmers
 (for details visit www.philips.com/ledtechguide for compatible leading edge dimmers).

Energy Efficiency

| Estimated Lighting Costs Using a Standard 60W Incandescent A19 Lamp | | |
|---|----------|--------------------------------------|
| Present Wattage | | 60 W |
| x Annual Operating Hours | | 4,000 hrs |
| | = | 240,000 watt-hours |
| ÷ 1,000 | = | 240 kWh per year |
| x kWh rate of \$0.11 | = | \$26.40 per year |
| x 100 lamps per space | = | \$2,640 annual energy cost per space |
| Estimated Lighting Costs Using a Philips 11W Philips A19 LED Lamp | | |
| Present Wattage | | 11 W |
| x Annual Operating Hours | | 4,000 hrs |
| | = | 44,000 watt-hours |
| ÷ 1,000 | = | 44 kWh per year |
| x kWh rate of \$0.11 | = | \$4.84 per year |
| x 100 lamps per space | = | \$484 annual energy cost per space |
| Total Estimated Annual Savings⁰ | = | \$2,156.00 |

⁰ Based on 100 lamps per space operating at 4,000 hours per year.

WARNINGS AND CAUTIONS

- Suitable for damp locations.
- Not for use in totally enclosed luminaires (fixtures).
- This device is not intended for use with emergency exit fixtures or emergency lights.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

CAUTION: Risk of electric shock. Do not use where directly exposed to water.

NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:
 (1) This device may not cause harmful interference, and
 (2) This device must accept any interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-003.

This energy saving example shows an application of 100 lamps in a space currently using 100 incandescent 60W, 800 lumen A19 lamps, operating 4,000 hours per year at a cost of \$0.11 per kWh.[‡] Your actual savings may vary depending on the energy costs in your geographic location.

Replacing 100 standard incandescent 60W 800 lumen A-lamps with Philips 11W Philips LED A19 lamps can provide significant energy cost savings of \$2,156 per year! Potential savings from the reduction in HVAC costs as a result of using a lower wattage lamp that emits less heat is an additional benefit not included in this example.

[‡] Light output of the 11W Philips A19 with 830 lumens compares to the 60W standard incandescent A19 with 800 lumens



© 2013 Philips Lighting Company.
 A Division of Philips Electronics North America Corporation.
 All rights reserved.
 Printed in USA 1/13
 P-6466
www.philips.com

Philips Lighting Company
 200 Franklin Square Drive
 Somerset, NJ 08873
 1-800-555-0050

Philips Lighting
 281 Hillmount Road
 Markham, Ontario
 Canada L6C 2S3
 1-800-555-0050
 A Division of Philips Electronics Ltd.