



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL 40W/10 1SL

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Product data

• General Characteristics

| | |
|----------------------|-------------|
| System Description | Rapid Start |
| Cap-Base | G13 |
| Bulb | T12 |
| Main Application | Reprography |
| Useful Life | 5000 hr |
| Life to 50% failures | 9000 hr |
| EM | |

• Light Technical Characteristics

| | |
|---------------------------|---------|
| Color Code | 10 |
| Color Designation (text) | Actinic |
| Chromaticity Coordinate X | 222 - |
| Chromaticity Coordinate Y | 210 - |
| Depreciation 5000 hours | 40 % |
| Depreciation 2000 hours | 20 % |

• Electrical Characteristics

| | |
|------------------------|--------|
| Lamp Wattage | 40 W |
| Lamp Wattage Technical | 39 W |
| Lamp Voltage | 101 V |
| Lamp Current | 0.43 A |

• Environmental Characteristics

| | |
|----------------------|---------|
| Mercury (Hg) Content | 13.0 mg |
|----------------------|---------|

• UV-related Characteristics

| | |
|----------------------------|--------|
| UV-A Radiation 100hr (IEC) | 10.0 W |
| UV-B/UV-A (IEC) | 0.2 % |
| UV-A Radiation 0hr (IEC) | 12.4 W |

• Product Dimensions

| | |
|--------------------------|-------------------------------|
| Base Face to Base Face A | 1199.4 (max) mm |
| Insertion Length B | 1204.1 (min), 1206.5 (max) mm |
| Overall Length C | 1213.6 (max) mm |
| Diameter D | 40.5 (max) mm |



• Product Data

| | |
|-----------------------------|-----------------------------|
| Order code | 928011301020 |
| Full product code | 928011301020 |
| Full product name | Actinic BL TL 40W/10 SLV |
| Order product name | Actinic BL TL 40W/10 SLV/25 |
| Pieces per pack | 1 |
| Packing configuration | 25 |
| Packs per outerbox | 25 |
| Bar code on pack - EAN1 | 8711500260260 |
| Bar code on outerbox - EAN3 | 8711500260277 |
| Logistic code(s) - 12NC | 928011301020 |
| Net weight per piece | 292.000 gr |

Actinic BL TL(-K)/TL-D(-K)



Dimensional drawing

| Product | A (Max) | B (Min) | B (Max) | C (Max) | D (Max) |
|--------------|---------|---------|---------|---------|---------|
| TL 40W/10 RS | 1199.4 | 1204.1 | 1206.5 | 1213.6 | 40.5 |



G13

Photometric data



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, September 8
data subject to change