

# Energy Saver Decoratives

## 5W EL/Can T2

Philips Energy Saver Decorative CFLs provide energy savings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

### Product data

#### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Bulb	EL/Can T2
Rated Lifetime (hours)	8000 hr

#### • Light Technical Characteristics

Color Code	827 [CCT of 2700K]
Color Rendering Index	80 (min) Ra8
Color Designation	Warm White
Color Temperature	2700 K
Color Temperature technical	2700 K
Rated Luminous Flux	215 Lm
Luminous Efficacy Lamp	43 Lm/W
Lumen Maintenance 2000h	80 %
Lumen Maintenance 5000h	70 %
Chromaticity Coordinate X	459 -
Chromaticity Coordinate Y	412 -

#### • Electrical Characteristics

Watts	5 W
Power Factor	0.55 -
Voltage	110-127 V
Lamp Current mA	90 mA

Line Frequency	50/60 Hz
Dimmable	No
Starting Time	0.2 s
Warm-up Time to 60% Light Outp	180 (max) s

#### • Environmental Characteristics

Energy Efficiency Label (EEL)	A
-------------------------------	---

#### • Measuring Conditions

Switching cycle	5000X
-----------------	-------


#### • Product Dimensions

Overall Length C	103.8 (max) mm
Diameter D	40.5 (max) mm
Width F	40 (max) mm

#### • Product Data

Product number	422295
Full product name	5W EL/Can T2
Short product name	EL/Can T2 5W
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677422295
Bar code on case	50046677422290
Logistics code(s)	929689962701
eop_net_weight_pp	0.047 kg

Dimensional drawing



E26

5W EL/Can T2

Product	C (Max)	D (Max)	F (Max)
Candle 5W E26 110-127V 50/60Hz EL/Can T2	103.8	40.5	40



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, December 11  
data subject to change