

Philips A-shape
Dimmable LED Lamp

Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, government buildings, and multi-unit residences

LED



Attractive, dimmable LED alternative to popular incandescents

Philips A-shape Dimmable LED Lamps are the smart LED alternative to standard incandescent A-shape lamps. The unique lamp design provides omni-directional light with excellent dimming performance.

High efficacy LED accent light

- New bulb shape to compliment fixtures and decor
- 8W A19 LED bulb is ENERGY STAR® Qualified and replaces a 40W incandescent equivalent A19 bulb*
- 11W A19 LED bulb is ENERGY STAR® Qualified and replaces a 60W incandescent equivalent A19 bulb**
- Smooth dimming to 10% of full light levels†
- 25,000 hour rated average life‡
- Emits virtually no UV/IR in the light beam
- Contains no mercury

Easy to experience

- Long life properties—lowers maintenance costs by reducing re-lamp frequency
- Will not fade colors, avoids inventory spoilage
- 3-year limited warranty***



PHILIPS

Philips A-shape Dimmable LED Lamp

Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Ordering Code	Norm. Watts	Volts	Lamps per SKU	Description	Bulb Type	Base	Rated Avg. Life (Hrs.) ¹	Approx. Lumens ²	CRI	Color Temp. (Kelvin)	MOL (In.)
A19												
42348-3	8A19/END/2700 DIM 6/1	8	120	1	120V Bulb END 8-40W 2700K 470 Dim SOC	A19	Med	25000	470	81	2700	4
42349-1	11A19/END/2700 DIM 6/1	11	120	1	120V Bulb END 11-60W 2700K 830 Dim SOC	A19	Med	25000	830	81	2700	4

Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H)(In.)	Case Dimensions (W x D x H)(In.)	Pallet Dimensions (W x D x H)(In.)
A19											
42348-3	42348-3	42348-8	6	2.45	0.131	1224	204	6	2.72 x 2.72 x 4.80	8.40 x 5.60 x 4.80	47.20 x 39.40 x 34.90
42349-1	42349-0	42349-5	6	2.45	0.131	1224	204	6	2.72 x 2.72 x 4.80	8.40 x 5.60 x 4.80	47.20 x 39.40 x 34.90

- 1) Rated average life is based on engineering testing and probability analysis.
 2) Based on photometric testing consistent with IES LM-79.
 ■ This lamp is ENERGY STAR® Qualified.

- Footnotes from front:
 * When comparing a 8W LED A19 having 470 lumens to the standard 40W incandescent A19 having 500 lumens.
 ** When comparing a 11W LED A19 having 830 lumens to the standard 60W incandescent A19 having 800 lumens.
 *** For details see: http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd.
 † Dimmable when using leading edge dimmers
 (for details visit www.philips.com/ledtechguide for compatible leading edge dimmers).

Energy Efficiency

Estimated Lighting Costs Using a Standard 60W Incandescent A19 Lamp		
Present Wattage		60 W
x Annual Operating Hours		4,000 hrs
	=	240,000 watt-hours
÷ 1,000	=	240 kWh per year
x kWh rate of \$0.11	=	\$26.40 per year
x 100 lamps per space	=	\$2,640 annual energy cost per space
Estimated Lighting Costs Using a Philips 11W Philips A19 LED Lamp		
Present Wattage		11 W
x Annual Operating Hours		4,000 hrs
	=	44,000 watt-hours
÷ 1,000	=	44 kWh per year
x kWh rate of \$0.11	=	\$4.84 per year
x 100 lamps per space	=	\$484 annual energy cost per space
Total Estimated Annual Savings[§]	=	\$2,156.00

[§] Based on 100 lamps per space operating at 4,000 hours per year.

WARNINGS AND CAUTIONS

- Suitable for damp locations.
- Not for use in totally enclosed luminaires (fixtures).
- This device is not intended for use with emergency exit fixtures or emergency lights.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

CAUTION: Risk of electric shock. Do not use where directly exposed to water.

NOTES: This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:
 (1) This device may not cause harmful interference, and
 (2) This device must accept any interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-003.

This energy saving example shows an application of 100 lamps in a space currently using 100 incandescent 60W, 800 lumen A19 lamps, operating 4,000 hours per year at a cost of \$0.11 per kWh.[‡] Your actual savings may vary depending on the energy costs in your geographic location.

Replacing 100 standard incandescent 60W 800 lumen A-lamps with Philips 11W Philips LED A19 lamps can provide significant energy cost savings of \$2,156 per year! Potential savings from the reduction in HVAC costs as a result of using a lower wattage lamp that emits less heat is an additional benefit not included in this example.

[‡] Light output of the 11W Philips A19 with 830 lumens compares to the 60W standard incandescent A19 with 800 lumens



© 2013 Philips Lighting Company.
 A Division of Philips Electronics North America Corporation.
 All rights reserved.
 Printed in USA 1/13
 P-6466
www.philips.com

Philips Lighting Company
 200 Franklin Square Drive
 Somerset, NJ 08873
 1-800-555-0050

Philips Lighting
 281 Hillmount Road
 Markham, Ontario
 Canada L6C 2S3
 1-800-555-0050
 A Division of Philips Electronics Ltd.