

HALOGEN LAMPS

Energy Advantage IR PAR38 Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.	Description	Class, Filament	MOL (In.)	Rated Avg. Life (Hrs.) ⁽⁹³⁾	Approx. MBCP*	Lumens
-------	------	------	----------------	--------------------	---------------	-------	-----------	-------------	-----------------	-----------	--	---------------	--------

HALOGEN ENERGY ADVANTAGE IR PAR38 LAMPS FEATURING HALOGEN INFRARED TECHNOLOGY AND DIOPTIC REFLECTOR (82, 86)

LOWER WATTAGE ENERGY SAVING LAMPS														
40	PAR38	Med.Skt.	14502-9	\$	⊕	40PAR38/IRC/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	4200	11,000	720
	Dioptic		14503-7	\$	⊕	40PAR38/IRC/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	4200	3000	720
	Reflector		14504-5	\$	⊕	40PAR38/IRC/HAL/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	1050	720
50	PAR38	Med.Skt.	14505-2	\$	⊕	50PAR38/IRC/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	4200	15,500	970
	Dioptic		14506-0	\$	⊕	50PAR38/IRC/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	4200	4000	970
	Reflector		14507-8	\$	⊕	50PAR38/IRC/HAL/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	1500	970
60	PAR38	Med.Skt.	13873-5	\$	⊕	60PAR38/IRC/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	4200	15,500	1120
	Dioptic		13874-3	\$	⊕	60PAR38/IRC/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	4200	5100	1120
	Reflector		13875-0	\$	⊕	60PAR38/IRC/HAL/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	1800	1120
70	PAR38	Med.Skt.	13861-0	\$	⊕	70PAR38/IRC/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	4200	17,800	1550
	Dioptic		13862-8	\$	⊕	70PAR38/IRC/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	4200	6170	1550
	Reflector		13863-6	\$	⊕	70PAR38/IRC/HAL/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	2320	1550
100	PAR38	Med.Skt.	13876-8	\$	⊕	100PAR38/IRC/HAL/SP10	120	12	Spot 10°	C, CC-8	5%	4200	26,400	2200
	Dioptic		13877-6	\$	⊕	100PAR38/IRC/HAL/FL25	120	12	Flood 25°	C, CC-8	5%	4200	8500	2200
	Reflector		13878-4	\$	⊕	100PAR38/IRC/HAL/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	3500	2200

HALOGEN ENERGY ADVANTAGE IR PLUS HALOGEN PAR38 LAMPS

39	PAR38	Med.	23844-4			39PAR38/IRC+/SP10	120	12	Spot 10°	C, CC-8	5%	4200	11,000	720
			23845-1			39PAR38/IRC+/FL25	120	12	Flood 25°	C, CC-8	5%	4200	2500	720
55	PAR38	Med.	23847-7			55PAR38/IRCE/SP10	120	12	Spot 10°	C, CC-8	5%	4200	16,500	1120
			23865-9			55PAR38/IRCE/FL25	120	12	Flood 25°	C, CC-8	5%	4200	4100	1120
			23849-3			55PAR38/IRCE/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	1800	1120
83	PAR38	Med.	23850-1			83PAR38/IRC+/SP10	120	12	Spot 10°	C, CC-8	5%	4200	25,000	2000
			23851-9			83PAR38/IRC+/FL25	120	12	Flood 25°	C, CC-8	5%	4200	7000	2000
			23852-7			83PAR38/IRC+/WFL40	120	12	Wide Flood 40°	C, CC-8	5%	4200	3000	2000

HALOGEN ENERGY ADVANTAGE IR PAR38 LAMPS 130V FEATURING HALOGEN INFRARED TECHNOLOGY AND DIOPTIC REFLECTOR (82, 86)

60	PAR38	Med.Skt.	13920-4	\$	⊕	60PAR38/IRC/HAL/SP10	130	12	Spot 10°	C, CC-8	5%	4200	15,500	1120
										Ratings @ 120V=53W		8400	—	880
	Dioptic	Reflector	13879-2	\$	⊕	60PAR38/IRC/HAL/FL25	130	12	Flood 25°	C, CC-8	5%	4200	5100	1120
										Ratings @ 120V=53W		8400	—	880
			13918-8	\$	⊕	60PAR38/IRC/HAL/WFL40	130	12	Wide Flood	C, CC-8	5%	4200	1800	1120
									Ratings @ 120V=53W		8400	—	880	

For the most current product information go to the e-catalog on www.philips.com
Halogen symbol and footnotes located on page 116



Energy Advantage
IR PAR38
Med. Skt.