



# Specialty Lamps

## Sealed Beam, Ceramic ST, Short Arc and Fluorescent Lamps with Super Actinic Radiation

Product Number	Watts	Description	Volts	Base	Diam. (In.)	Diam. (mm)	MOL (In.)	MOL (mm)	Lumens	Rated Avg. Life (Hrs.)*	Color Temp. (K)	Burning Position	Beam Shape
----------------	-------	-------------	-------	------	-------------	------------	-----------	----------	--------	-------------------------	-----------------	------------------	------------

### Sealed Beam

27357-3	300	300PAR56/NSP	240	Mog. End	7	178	5	127		2000	3000	Universal	Narrow Spot
27356-5	300	300PAR56/MFL	240	Mog. End	7	178	5	127		2000	3000	Universal	Med. Flood
27358-1	300	300PAR56/WFL	240	Mog. End	7	178	5	127		2000	3000	Universal	Wide Flood
35619-6	500	500PAR56Q/NSP	120	Mog. End	7	179	5	127	88,000	4000	2950	Universal	Narrow Spot
35621-2	500	500PAR56Q/MFL	120	Mog. End	7	179	5	127	43,000	4000	2950	Universal	Med. Flood
35620-4	500	500PAR56Q/WFL	120	Mog. End	7	179	5	127	22,500	4000	2950	Universal	Wide Flood
27360-7	1000	1000PAR64/VNSP	240	Mog. End	8	204	6	150		300	3200	Universal	Very Narrow Spot
27361-5	1000	1000PAR64/NSP	240	Mog. End	8	204	6	150		300	3200	Universal	Narrow Spot
27362-3	1000	1000PAR64/MFL	240	Mog. End	8	204	6	150		300	3200	Universal	Med. Flood

Description	Product Number	Watts	Volts	Lamp Current (Amps)	Initial Lumens	Rated Avg. Life (Hrs.)*	Arc Length (mm)	CRI	Color Temp (K)	Base
-------------	----------------	-------	-------	---------------------	----------------	-------------------------	-----------------	-----	----------------	------

### Ceramic ST Lamps

Ceramic ST 250HR	24517-5	250	100	2.6	23,000	4000	8	90	3200	GZY9.5
------------------	---------	-----	-----	-----	--------	------	---	----	------	--------

Product Number	Description	Watts	Volts	Lumens	Base	LCL (In.)	MOL (In.)
----------------	-------------	-------	-------	--------	------	-----------	-----------

### Short Arc Lamps<sup>(1)</sup>

31644-8	SAH250B	250	42	10,000	Med. Pf.	3.0	6
38278-8	CDM-SA/R 150W/942	150	96	—	G12	2.2	4
36039-6	CDM-SA/T 150W/942	150	96	14,000	G12	2.2	4

Product Number	Description	Watts	Current Amps	Bulb	Nom. Length (mm)	(In.)
----------------	-------------	-------	--------------	------	------------------	-------

### Fluorescent Lamps with Super Actinic Radiation—Medium BiPin Base

30808-0	TLI40W/03	140	1.46	T12	1514	60
---------	-----------	-----	------	-----	------	----

1) DC operation only—should be operated on a control circuit which supplies direct current to the lamp.

\* Rated Average Life is the length of operation (in hours) at which point 50% of a large sample of lamps will still be operational and 50% will not. Unless otherwise noted all dimensions are in inches. To convert inches to millimeters multiply by 25.4001.

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)



PAR56  
Mog. End Base



Ceramic ST 250 HR  
GZY9.5 Base



Ceramic ST 250  
Mini FastFit  
PGJX28 Base



SAH 250 B



TL  
TLK