

# Reflector Agro

Agro 75W 120V BR30CDA

Philips Family of Reflector Agro provide the perfect light to promote plant growth.

## Product data

### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	BR30
Bulb Finish	Agro-Blue
Filament Shape	CC6 [Straight]
Operating Position	Universal [Any or Universal (U)]
Main Application	Agro
Atmosphere	Gas
Life with 3h/day use [years]	1.8 an
Estimated Energy Cost/YR	9.03 \$

### • Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	55 D
Initial lumen	700 Lm

### • Electrical Characteristics

Watts	75 W
Voltage	120 V

### • Product Dimensions

Max Overall Length (MOL) - C	5.375 (max) in
------------------------------	----------------

Diameter D 3.75 in

### • Footnotes

Footnotes Incandescent	87 [Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)]
Footnotes Incandescent	920 [Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.]


### • Product Data

Product number	415281
Full product name	Agro 75W 120V BR30CDA
Short product name	75BR30/ARGO CDA 120V 6/1 TP
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677415280
Bar code on case	50046677415285
Logistics code(s)	920682436307
eop_net_weight_pp	0.011 kg


# PHILIPS

sense and simplicity

## Dimensional drawing



Agro 75W 120V BR30CDA



Agro 75W 120V BR30CDA



E26



© 2013 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2013, January 31  
data subject to change