

Energy Advantage IR PAR38



Energy Advantage IR 70W 120V PAR38 DiOptic FL 25D
CL 1CT

Philips Halogen Energy Advantage IR PAR Lamps combine visual appeal with energy savings and long life. These lamps provide high quality light that bring out textures in clothes and linens.

Product data

• General Characteristics

Base	Medium Skirted [Skirted Medium Screw (PAR Lamps)]
Base Information	Brass [Brass Base]
Bulb	PAR38 DiOptic
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Outdoor
Atmosphere	Gas
RatedAvgLife(See Family Notes)	4200 hr

• Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	25 D
Approx. MBCP	6170 cd
Color Rendering Index	100 Ra8
Color Temperature	2900 K
Initial lumen	1550 Lm

• Electrical Characteristics

Watts	70 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	5.313 (max) in
Diameter D	4.75 in

• Product Data

Product number	138628
Full product name	Energy Advantage IR 70W 120V PAR38 DiOptic FL 25D CL 1CT
Short product name	70W 120V PAR38 DiOptic FL 25D CL 1CT
Pieces per Sku	1
Skus/Case	12
Bar code on pack	046677138622
Bar code on case	50046677138627
Logistics code(s)	924757119670

Dimensional drawing


PHILIPS

sense and simplicity

Dimensional drawing

E26, PAR38

Product	C (Max)	D (Norm)
PAR38 IRC 70W E26/50x39 120V FL 25D	5.313	4.75



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change