



Reflector Flood

Reflector 65W 120V BR40 FL 60D 1WR

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	BR40
Bulb Finish	Frosted
Filament Shape	CC6 [Straight]
Operating Position	Base Up Horizontal (BUH) [Hanging +/-90D or Base Up HOR (BUH)]
Main Application	Flood and Ambient Lighting
Atmosphere	Gas
Estimated Energy Cost/YR	7.83 \$
Life with 3h/day use [years]	1.8 an

• Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	60 D
Color Temperature	2710 K
Initial lumen	620 Lm

• Electrical Characteristics

Watts	65 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	6.5 (max) in
------------------------------	--------------

Diameter D 5 in


• Footnotes

Footnotes Incandescent 87 [Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)]


• Product Data

Product number	389130
Full product name	Reflector 65W 120V BR40 FL 60D 1WR
Short product name	Refl 65W 120V BR40 FL 60D 1WR
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677225360
Bar code on case	50046677389135
Logistics code(s)	920670036324
eop_net_weight_pp	0.001 kg

Dimensional drawing



E26, BR40



E26, BR40



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change