



DuraMax Reflector Flood

DuraMax 65W 130V BR40 FL 60D CDA 1WR

Philips DuraMax® Long Life Reflector Flood Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Available in a variety of sizes and wattages. Use flood lights for general or ambient lighting; use spot lights to highlight artwork or architecture. Both are ideal for use in recessed cans or track lighting fixtures.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	BR40
Bulb Finish	Frosted
Filament Shape	CC6 [Straight]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
Rated Avg. Life @ 120v	4000 hr
Estimated Energy Cost/YR	7.83 \$
Life with 3h/day use [years]	1.8 an

• Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	60 D
Color Temperature	2750 K
Initial lumen	565 Lm
Initial Lumens @ 120V	425 Lm

• Electrical Characteristics

Watts	65 W
Voltage	130 V

• Product Dimensions

Max Overall Length (MOL) - C	6.5 (max) in
------------------------------	--------------

Diameter D 5 in


• Footnotes

Footnotes Incandescent	905 [Consider the compact fluorescent lamps for energy savings.]
Footnotes Incandescent	87 [Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)]


• Product Data

Product number	225375
Full product name	DuraMax 65W 130V BR40 FL 60D CDA 1WR
Short product name	DuraMax 65W 130V BR40 FL 60D CDA 1WR
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677225377
Bar code on case	50046677225372
Logistics code(s)	920670336103
eop_net_weight_pp	0.001 kg

Dimensional drawing



E26, BR40



E26, BR40



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change