

Reflector Agro

Agro 75W 120V BR30 FL 55D AgroCDA 1CT

Philips Family of Reflector Agro provide the perfect light to promote plant growth.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	BR30
Bulb Finish	Agro-Blue
Filament Shape	CC6 [Straight]
Operating Position	Universal [Any or Universal (U)]
Main Application	Agro
Atmosphere	Gas
Estimated Energy Cost/YR	9.03 \$
Life with 3h/day use [years]	1.8 an

• Light Technical Characteristics

Beam Description	Flood [Flood]
Beam Angle	55 D
Initial lumen	700 Lm

• Electrical Characteristics

Watts	75 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	5.375 (max) in
------------------------------	----------------

Diameter D 3.75 in

• Footnotes

Footnotes Incandescent	87 [Do not allow hot bulb to come in contact with liquid or metal parts of the fixture, as glass may shatter. Do not use outdoors. Do not operate in close proximity to flammable materials or those adversely affected by heat or drying. Operate only in heat resistant sockets. (87)]
Footnotes Incandescent	920 [Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.]


• Product Data

Product number	249052
Full product name	Agro 75W 120V BR30 FL 55D AgroCDA 1CT
Short product name	Agro 75W 120V BR30 FL 55D AgroCDA 1CT
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677227432
Bar code on case	50046677227437
Logistics code(s)	920682436306
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity

Dimensional drawing



E26, BR30



E26, BR30



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change