



Reflector Flood

Reflector 300W Med 120V BR40 FL FR 1CT

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Aluminum [Aluminum Base]
Bulb	BR40
Bulb Finish	Frosted
Filament Shape	C11 [V-shape above glass button (cylindrical)]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
Circle E logo	Yes

• Light Technical Characteristics

Beam Description	Flood [Flood]
Initial lumen	2480 Lm

• Electrical Characteristics

Watts	300 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	6.5 (max) in
------------------------------	--------------

Diameter D 5 in


• Footnotes

Footnotes Incandescent 920 [Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.]


• Product Data

Product number	143438
Full product name	Reflector 300W Med 120V BR40 FL FR 1CT
Short product name	Refl 300W Med 120V BR40 FL FR 1CT
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677143435
Bar code on case	50046677143430
Logistics code(s)	920673035502
eop_net_weight_pp	0.001 kg

Dimensional drawing



E26, BR40



E26, BR40



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change