



Swimpool

Reflector 300W Med 120V R40 FL FR 1CT

The Philips Family of Swimpool lamps are incandescent, gas-filled reflector flood lamps specifically designed for swimming pools and underwater applications.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Nic/Brass [Nickel/Brass Base]
Bulb	R40
Bulb Finish	Frosted
Filament Shape	CC11 [V-shape above glass button (cylindriform)]
Operating Position	Horizontal [Parallel or Horizontal(HOR)]
Main Application	Underwater
Atmosphere	Gas
Circle E logo	Yes

• Light Technical Characteristics

Beam Description	Flood [Flood]
Initial lumen	2480 Lm

• Electrical Characteristics

Watts	300 W
Voltage	120 V

• Product Dimensions

Max Overall Length (MOL) - C	6.75 (max) in
------------------------------	---------------

Diameter D 5 in

• Footnotes


Footnotes Incandescent	920 [Circle E-The encircled E means this bulb meets Federal minimum efficiency standards.]
------------------------	--

• Product Data

Product number	144295
Full product name	Reflector 300W Med 120V R40 FL FR 1CT
Short product name	Refl 300W Med 120V R40 FL FR 1CT
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677144296
Bar code on case	50046677144291
Logistics code(s)	920673434302
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing



E26/E39, R40

Product	C (Max)	D (Norm)
300W E26 120V R40 FL	6.75	5



E26



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, July 31
data subject to change