



ALR 37/56 mm

GBF 20W 12V R37 32D FR 1CT

Delivers high lumen output and excellent color rendering for precise accent and display lighting. Philips Halogen Aluminum Reflector Lamps provide continuous color and high luminous intensity for precise accent and display lighting. These lamps offer a rated average life ranging from 2000 hours and feature excellent beam qualities for accent or ambient lighting.

Product data

• General Characteristics

Philips Code	6435/FR
ANSI Code Halogen	GBF
Base	Double Contact Bayonet
Base Information	19
Bulb	R37 [R 37mm]
Bulb Finish	Frosted
Operating Position	Universal [Any or Universal (U)]
RatedAvgLife(See Family Notes)	2000 hr

• Light Technical Characteristics

Beam Angle	32 D
Beam Angle Technical	32 D
Approx. MBCP	350 (max) cd
Color Rendering Index	100 Ra8
Color Temperature	3000 K
Color Temperature technical	3000 K

• Electrical Characteristics

Watts	20 W
Lamp Wattage Technical	20.0 W
Voltage	12 V
Lamp Current	1.67 A

Dimmable Yes

• Luminaire Design Requirements

Cap-Base Temperature	350 (max) C
Bulb Temperature	450 (max) C

• Product Dimensions


Overall Length C	41 (max) mm
Diameter D	38 (max) mm

• Product Data

Product number	340034
Full product name	GBF 20W BA15d 12V R37 32D FR 1CT
Short product name	GBF 20W BA15d 12V R37 32D FR 1CT/10X5F
Pieces per Sku	1
eop_pck_cfg	10X5F
Skus/Case	50
Bar code on pack	46677340032
Bar code on intermediate pack	30046677340033
Bar code on case	50046677340037
Logistics code(s)	924001517119
tpd_ilcos_cd	HMG1/F-20-12-B15d-37/32
eop_net_weight_pp	19.000 gr

Dimensional drawing

Dimensional drawing



B15/BA15d R37

Product	C (Max)	D (Max)
Alu 37mm 6435/FR 20W BA15d 12V 32D FR	41	38



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change