



MR16

ESX 20W GU5.3 12V MR16 10D 1CT

Philips Halogen MR16 lamps provide a bright white light for accent lighting. They make it easy to optimize the look and feel of your brand, your merchandise, and the shoppers experience, with lower operating costs.

Product data

• General Characteristics

Philips Code	14637
ANSI Code Halogen	ESX
Base	GU5.3
Bulb	MR16 [MR 16inch/50mm]
Operating Position	Universal [Any or Universal (U)]
RatedAvgLife(See Family Notes)	3000 hr
Rated Lifetime (hours)	3000 hr
Rated Lifetime (years)	3 an

• Light Technical Characteristics

Beam Angle	10 D
Beam Angle Technical	10 D
Approx. MBCP	3400 (max) cd
Color Rendering Index	100 Ra8
Color Temperature	3000 K
Color Temperature technical	3000 K

• Electrical Characteristics

Watts	20 W
Lamp Wattage Technical	20.0 W
Voltage	12 V
Lamp Current	1.67 A
Dimmable	Yes

• Environmental Characteristics

Energy Efficiency Label (EEL)	-
Mercury (Hg) Content	0.0 mg

• Luminaire Design Requirements

Cap-Base Temperature	350 (max) C
Bulb Temperature	250 (max) C

• Product Dimensions

Overall Length C	46 (max) mm
Diameter D	50 (max) mm



• Product Data

Product number	378026
Full product name	ESX 20W GU5.3 12V MR16 10D 1CT
Pieces per Sku	1
eop_pck_cfg	10X5F
Skus/Case	50
Bar code on pack	46677378028
Bar code on intermediate pack	2005040008090
Bar code on case	50046677378023
Logistics code(s)	924053217122
tpd_ilcos_cd	HRGI-20-12-GU5.3-50/10
eop_net_weight_pp	23.500 gr

PHILIPS

sense and simplicity

Dimensional drawing



GU5.3

GU5.3, MR16

Product	C (Max)	D (Max)
FIGHTER 14637 20W GU5.3 12V MR16 10D	46	51



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change