

# PAR30S

50W 130V PAR30S SP 10D 1CT

Philips Halogen PAR lamps will provide bright, white light across the product line and feature excellent beam qualities for accent or ambient lighting. Their optimized coil and burner design allows for clear, crisp lighting effects with excellent color rendering, making it easy to optimize the look and feel of your store and your merchandise.

## Product data

### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Base Information	Brass [Brass Base]
Bulb	PAR30S [PAR 3.75 inch/95mm Short]
Bulb Material	Hard Glass
Bulb Finish	Clear
Reflector Finish	Aluminized
Filament Shape	CC-8 [Axial]
Operating Position	Universal [Any or Universal (U)]
Main Application	Indoor Reflector
Atmosphere	Gas
RatedAvgLife(See Family Notes)	2000 hr
Rated Avg. Life @ 120v	4000 hr
Estimated Energy Cost/YR	6.02 \$
Life with 3h/day use [years]	1.8 an

### • Light Technical Characteristics

Beam Description	Spot
Beam Angle	10 D
Approx. MBCP	7100 cd
Color Rendering Index	100 Ra8
Color Temperature	2820 K

Initial lumen	630 Lm
Initial Lumens @ 120V	480 Lm
Approx MBCP@120v	5680 cd

### • Electrical Characteristics

Watts	50 W
Voltage	130 V

### • Product Dimensions

Max Overall Length (MOL) - C	3.625 (max) in
Diameter D	3.75 in


### • Product Data

Product number	263574
Full product name	50W 130V PAR30S SP 10D 1CT
Short product name	50W 130V PAR30S SP 10D 1CT
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677263577
Bar code on case	50046677263572
Logistics code(s)	924757105203
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

Dimensional drawing



E26, PAR30S



E26, PAR30S



E26



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change